



CATALOG NUMBER: See table below
DESCRIPTION: Cube tap extension cord
APPROVALS: UL/CUL Listed General-Use Cord Set

CONSTRUCTION PARAMETERS:

Cable type: 16/2 SPT-2
Cable length: See table below
Attachment plug configuration: NEMA 1-15P (polarized)
Cord connector configuration: NEMA 1-15R x3 (polarized)
Plug and connector material: Molded PVC
Color: See table below

**ENVIRONMENTAL AND ELECTRICAL PROPERTIES:**

Cord set application: Indoor use only
Nominal operating voltage: 125 VAC
Maximum operating current: 13 A
Maximum operating wattage: 1625 W

CATALOG NUMBERS:

Catalog number	Length	Color	Case qty	UPC
94018907	6 ft	Brown	48	0 29892 09401 0
94028907	9 ft	Brown	36	0 29892 09402 7
94038907	12 ft	Brown	36	0 29892 09403 4
94048907	15 ft	Brown	24	0 29892 09404 1
94058907	20 ft	Brown	24	0 29892 09405 8
94118901	6 ft	White	48	0 29892 09411 9
94128901	9 ft	White	36	0 29892 09412 6
94138901	12 ft	White	36	0 29892 09413 3
94148901	15 ft	White	24	0 29892 09414 0
94158901	20 ft	White	24	0 29892 09415 7

This product complies with European Directive 2011/65/EU (RoHS-2)

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part.

We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is the proprietary intellectual property of Southwire Company LLC. Any information contained herein shall not be disclosed to any party without the written consent of Southwire Company LLC.