




CATALOG NUMBER: See table below
DESCRIPTION: 6/3 & 8/1 SEOW, 125/250V 50A outdoor use cord set with "California Standard" twist-to-lock plug and cord connector

CONSTRUCTION PARAMETERS:

Conductors: (3) 6 AWG, 96/26 bunched bare copper
 (1) 8 AWG, 96/28 bunched bare copper
 Jacket material: TPE, black
 Overall cable O.D. (nom): 0.868"



CS6364L

CS6365L

Plug and connector manufacturer: Hubbell Wiring Device
 Plug and connector configuration: 50A 125/250V 3 pole 4 wire grounding, non-NEMA "California Standard"
 Plug and connector materials: Nylon body and backshell
 Neoprene cord gasket
 Stainless steel plug shroud

PROPERTIES:

Temperature rating of cable: -40 to +90 deg C
 Electrical ratings: 125/250 VAC, 50A

Catalog number	Length	Case qty	UPC
19370008	25 ft	2	0 29892 01937 2
19180008	50 ft	1	0 29892 01918 1
19190008	100 ft	1	0 29892 01919 8

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part.

We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is the proprietary intellectual property of Southwire Company, LLC. Any information contained herein shall not be disclosed to any party without the written consent of Southwire Company, LLC.