

Model # SDQ2P4, SDQ2P1-1/2

#2 SQUARE TIP SCREWDRIVER

Southwire's screwdrivers are designed for the professional with durability, quality and comfort in mind.



CLEAR IDENTIFICATION

Handle end is marked for easy identification of tip type and size

COMFORTABLE GRIP

Comfortable cushioned grip allows firm grip and greater torque

PRECISION TIP

Precision-machined, black phosphate coated tip reduces slipping

TWIST-RESISTANT

Integral flanges provide a solid, twist-resistant blade anchor

RELIABLE

Chrome-plated, steel shaft for maximum torque with less shaft twisting

southwiretools.com

BUILT FOR STRENGTH. BUILT FOR RELIABILITY.
BUILT FOR WORK.



Southwire™

FEATURES

- Chrome-plated, steel shaft for maximum torque with less shaft twisting
- Precision-machined, black Phosphate coated tip reduces slipping
- Comfortable cushioned grip allows firm grip and greater torque
- Integral flanges provide a solid, twist-resistant blade anchor
- Handle end is marked for easy identification of tip type and size
- Meets or exceeds the applicable ASME / ANSI specifications

SPECIFICATIONS

MODEL #	SD3/16CRD	SDQ2P4
STOCK #:	582842	582862
DESCRIPTION:	#2 SQ RECES TIP SCREWDRIVER 1-1/2" RD-SHANK	#2 RECESSED SQ SCRWDVR 4" SHANK
HEIGHT:	3.75"	8.5"
WIDTH:	1.25"	1.25"
DEPTH:	1.25"	1.25"
WEIGHT:	1.8 oz	3.8 oz
HEAD TYPE:	RECESSED SQUARE	RECESSED SQUARE
HEAD SIZE:	#2	#2
SHANK TYPE:	ROUND	ROUND
SHANK LENGTH:	1-1/2"	4"
HANDLE FINISH:	COMFORT GRIP	COMFORT GRIP

Southwire Company
One Southwire Drive
Carrollton, GA 30119



Southwire™



Customer Service: 1-855-SWTOOLS (855-798-6657)

Scan code to see more
Southwire Tools

southwiretools.com