



Crimping Pliers

THESE HIGH LEVERAGE CRIMPING PLIERS HAVE TWO DIE POSITIONS THAT PERMIT THE TOOL TO CRIMP INSULATED AND NON-INSULATED TERMINALS AND FERRULES



● **TAPERED NOSE**
for working in confined spaces

● **CRIMPS**
insulated and non-insulated terminals and connector

● **COMFORTABLE GRIP**
curved handle and ergonomic molded grip for comfortable use

● **HEAVY DUTY CUTTING**
specially-hardened wire cutter in nose

● **DIPPED GRIP**
curved handle and ergonomic dipped grip for comfortable use

- **CURVED HANDLE AND ERGONOMIC MOLDED OR DIPPED GRIP FOR COMFORTABLE USE**
- **10-22 AWG SOLDERLESS TERMINALS AND CONNECTORS**
- **CRIMPS INSULATED AND NON-INSULATED TERMINALS AND CONNECTORS**
- **SPECIALLY-HARDENED WIRE CUTTER IN NOSE**
- **TAPERED NOSE FOR WORKING IN CONFINED SPACES**

MODEL #	STOCK #	DESCRIPTION:	HEIGHT:	WIDTH:	DEPTH:	WEIGHT:	HANDLE FINISH	HANDLE COLOR	INSULATED AND NON-INSULATED CRIMPING CAPACITY
TCC9	589936	TERMINAL CRIMPER CUTTER	9.38"	1.88"	0.75"	13.7 oz	COMFORT GRIP	YELLOW/BLK	10-22 AWG SOLID (SOLDERLESS)
TCC9D	582899	TERMINAL CRIMPER CUTTER DIP HANDLE	9.75"	2.38"	0.63"	12.7 oz	DIPPED GRIP	YELLOW	10-22 AWG SOLID (SOLDERLESS)



Southwire™

Tools & Assembled Products Division

[BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.]

1-855-SWTOOLS
(855-798-6657)



Scan code to see more
Southwiretools.com