

Model # 10030S

## MANUAL RANGING MULTIMETER

This general purpose multimeter features a CAT III safety rating, rugged double molded housing, and a backlit display.



**EASY TO READ DISPLAY**  
Backlit digital display

**MULTI FUNCTION**  
7 functions with 20 ranges

**RUGGED DESIGN**  
Impact resistant double molded housing also provides comfortable grip

**BATTERY TESTING**  
Tests AAA, AA, C, D, 1.5 volt, button cell, and 9 volt batteries

### 7 FUNCTIONS

AC Voltage  
DC Voltage  
DC Current  
Resistance  
Battery Test  
Continuity  
Diode Test



[southwiretools.com](http://southwiretools.com)

BUILT FOR DURABILITY. BUILT FOR RELIABILITY.  
**BUILT FOR WORK.**



**Southwire™**

## FEATURES

- 7 functions with 20 ranges
- Backlit digital display
- Impact resistant double molded housing provides comfortable grip
- Integrated tilt-stand for easy viewing

## INCLUDES

- 10030S Multimeter
- Test leads
- 9 volt battery

## SPECIFICATIONS

MANUAL RANGING MULTIMETER (10030S)			
	Range	Max. Resolution	Basic Accuracy (% of reading)
AC Voltage:	600V	0.1V	±1.2%
DC Voltage:	600V	0.1mV	±0.8%
DC Current:	10A	1µA	±1.2%
Resistance:	2000kΩ	0.1Ω	±0.8%
Battery Test:	1.5V, 9V	10mV	±1.0%
Continuity:	Audible threshold: Approximately 30Ω		
Diode Test:	Yes		
Dimensions:	5.44 x 2.60 x 1.50 in.		
Weight:	370g		

**Test in low-light areas****Built-in tilt stand**

**Southwire Company**  
**One Southwire Drive**  
**Carrollton, GA 30119**



**Southwire™**



Scan code to see more  
 Southwire Tools

**southwiretools.com**

**Customer Service: 1-855-SWTOOLS (855-798-6657)**