

Model # 30010S

700 DEGREE FAHRENHEIT INFRARED THERMOMETER

Provides quick surface temperature measurements without contact. The ideal service tool for HVAC, mechanical and electrical maintenance.



ACCURATE READINGS

Laser pointer quickly identifies target

8:1 DISTANCE TO SPOT RATIO

At 8 inches, measures a 1" spot

EASY TO READ

Displays highest and lowest readings



southwiretools.com

BUILT FOR DURABILITY. BUILT FOR RELIABILITY.
BUILT FOR WORK.



Southwire™

Model # 30010S

700 DEGREE FAHRENHEIT INFRARED THERMOMETER

FEATURES

- 8 to 1 distance to spot ratio
- Displays highest and lowest readings
- Laser pointer identifies target
- Backlit display
- Simple operation

INCLUDES

- 30010S IR thermometer
- 9 volt battery

SPECIFICATIONS

700-DEG-F INFRARED THERMOMETER (30010S)	
Range:	-22°F to 700°F (-30° to 371°C)
Resolution:	0.1°F/°C
Basic Accuracy:	± 2% of reading or ±4°F/± 2°C, whichever is greater
Response Time:	Less than 1 second
Emissivity:	Fixed at 0.95
Distance to Spot Ratio:	8:1 (at 8" distance measures 1" spot)
Dimensions:	5.16 x 3.78 x 1.38 in.
Weight:	200g



Southwire Company
One Southwire Drive
Carrollton, GA 30119



Southwire™



Customer Service: 1-855-SWTOOLS (855-798-6657)

Scan code to see more
Southwire Tools

southwiretools.com