

Model # 51010S

## BORESCOPE INSPECTION CAMERA

Boreoscope inspection camera with 1 meter flexible gooseneck allows the user to probe behind walls, inside ventilation ducts and difficult to reach areas that are not otherwise accessible.



● **TIGHT SPACES - NO PROBLEM**

Flexible gooseneck can be configured for best viewing

● **MULTI USE**

Ideal for contractors and inspectors

● **CONVENIENT**

Uses standard AA batteries

● **IP67CAMERA WAND**

Waterproof and dustproof for harsh environments

● **SEE IN THE DARK**

Four powerful and adjustable LED lights illuminate dark spaces



[southwiretools.com](http://southwiretools.com)

BUILT FOR DURABILITY. BUILT FOR RELIABILITY.  
**BUILT FOR WORK.**



**Southwire™**

## FEATURES

- Great tool for maintenance and repair
- Four powerful and adjustable LED lights illuminate dark spaces
- Flexible gooseneck can be configured for best viewing
- Up to 2X digital zoom
- Auto Power-Off
- Includes (3) accessories that clip on to camera head
  - mirror
  - hook
  - magnet

## INCLUDES

- 51010S Borescope
- Extension tools: mirror, hook and magnet
- Four AA batteries

## SPECIFICATIONS

COMPACT BORESCOPE (51010S)	
Camera	
Maximum Resolution:	640 x 480
Maximum Frame Rate:	30 frames per second
Depth of Field:	0.4" (10mm) to infinity
Gooseneck Length:	39" (1m)
Camera Diameter:	0.66" (17mm)
TFT-LCD Display	
LCD Size:	2.4" (61mm)
Display Resolution:	480 (W) x 234 (H)
Power Supply:	4x "AA" Batteries
Dimensions:	9.46 x 6.30 x 3.94 in.



**Southwire Company**  
**One Southwire Drive**  
**Carrollton, GA 30119**



**Southwire™**



**Customer Service: 1-855-SWTOOLS (855-798-6657)**

Scan code to see more  
Southwire Tools  
**southwiretools.com**