

# MAXIS® FEEDER

A revolutionary new way to feed wire quickly and efficiently.



**FAST AND EFFICIENT**  
Quick 1 person setup and operate

**ADJUSTABLE**  
Easily adjust wire tension,  
even during operation

**VERSATILE**  
Handles wire sizes  
from 3/0 - 3 1/2" cable

**SUPERIOR GRIP**  
Grooved serpentine roller design  
for increased traction force

**HEAVY DUTY  
RUBBER WHEELS**  
Easy jobsite maneuverability and  
will never go flat

**INCREASED  
PULLING FORCE**  
1,600 lb capacity on  
4 - SIMpull THHN  
500 MCM conductors

[southwiretools.com](http://southwiretools.com)

BUILT FOR DURABILITY. BUILT FOR RELIABILITY.  
**BUILT FOR WORK.**



**Southwire™**

## FEATURES & BENEFITS

- Designed and built specifically to accommodate Southwire® SIMpull® wire
- Quick 1 person set-up and operate
- Forward and reverse, variable speed, feeds up to 30 fpm.
- May be used with Maxis Triggers® remote foot switches for simultaneous feeder/puller control
- Easily adjust wire tension, even during operation
- Fast 2 minute setup, wire sizes from 3/0 - 3 1/2" cable
- Solid rubber tires and swivel casters for easy jobsite maneuverability and will never go flat
- Digital footage meter allows easy monitoring of approx. conductor length being fed
- Uses grooved serpentine roller design with increased surface area for increased traction force (no pneumatic tires)
- Dual anchoring mechanism
- Maximum traction force: single conductor 800 lbs, 4 Conductors 1,600 lb capacity on SIMpull THHN 500 MCM
- Cable capacity: 8 x 250 MCM, 6 x 500 MCM, 5 x 750 MCM

## SPECIFICATIONS

| MODEL # | STOCK #  | DESCRIPTION  | HEIGHT | WIDTH | LENGTH | WEIGHT  |
|---------|----------|--------------|--------|-------|--------|---------|
| MCF01   | 58133301 | Cable Feeder | 35"    | 26"   | 44"    | 366 lbs |



**Southwire Company**  
**One Southwire Drive**  
**Carrollton, GA 30119**



**Southwire™**



Scan code to see more  
 Southwire Tools

**southwiretools.com**

**Customer Service: 1-855-SWTOOLS (855-798-6657)**