

MAXIS® TRIGGERS®

Dual remote foot switch

DUAL POWER CONTROL

Control puller from either end.

HIGH RANGE

Communicates up to 1500' between walls and up to 1.5 miles line of sight



FORCE GAUGE METER

Amp type force gauge monitors approximate pull tension

SAFETY

Stop the cable pull from either end immediately. Eliminate safety issues associated with feeding wire

southwiretools.com

BUILT FOR DURABILITY. BUILT FOR RELIABILITY.
BUILT FOR WORK.



Southwire™

FEATURES & BENEFITS

DUAL POWER CONTROL

- Each pedal has the ability to control the puller's power source
- Works with any Maxis® cable puller and most other pullers
- Saves time by avoiding unnecessary stops and restarts
- Helps reduce the risk of wire feeding mishaps

VISUAL COMMUNICATION

- LED lights on each footswitch indicate the cable pullers status
- Amp type force gauge- monitors pull tension based on the number of amps the motor is drawing. Useful when superior accuracy is not required (accuracy is +/- 20%). Amp usage is then translated into a tension reading shown on the display.

SAFETY

- Stop the cable pull from either end immediately
- No more audio miscommunication
- Increases safety by reducing issues associated with feeding wire

Range

- Amp type force gauge- monitors pull tension based on the number of amps the motor is drawing. Useful when superior accuracy is not required (accuracy is +/- 20%). Amp usage is then translated into a tension reading shown on the display.

RANGE

- Will communicate up to 1500' between walls and up to 1.5 miles line of sight 100' antenna extension available for added strength to your Triggers® communication

SPECIFICATIONS

MODEL #	STOCK#	HEIGHT	WIDTH	WEIGHT	LENGTH	DESCRIPTION
TR01	56824401	6.5"	16.5"	21 lbs	23.5"	DUAL REMOTE FOOT SWITCH



Southwire Company
One Southwire Drive
Carrollton, GA 30119



Southwire™



Customer Service: 1-855-SWTOOLS (855-798-6657)

Scan code to see more
Southwire Tools

southwiretools.com