

MAX PUNCH® MILD AND STAINLESS STEEL PUNCH AND DIES

Cleaner, quicker steel punch dies.

HEAVY DUTY CUTTING

Cuts through 10 gauge steel (3.5mm) as well as aluminum, fiberglass and plastics



QUICKER SMOOTHER CUT

Will not bow panel or leave jagged edges



HEAVY DUTY CUTTING

Cuts through 10 gauge stainless steel (3.5mm) as well as aluminum, fiberglass and plastics

QUICKER SMOOTHER CUT

Will not bow panel or leave jagged edges

southwiretools.com

BUILT FOR DURABILITY. BUILT FOR RELIABILITY.
BUILT FOR WORK.



Southwire™

SPECIFICATIONS

MAX PUNCH® MILD AND STAINLESS STEEL PUNCH AND DIES

CUPS & CUTTERS		CONDUIT & PIPE SIZE	HOLE SIZE ACTUAL "	MM	CAPACITY S.S. GA	
MPK050	56826301	1/2" conduit size cutter	1/2"	.89	23	10
MPC50	56827301	1/2" conduit size cup	1/2"	.89	23	10
MPK075	56826401	3/4" conduit size cutter	3/4"	1.12	28	10
MPC75	56827401	3/4" conduit size cup	3/4"	.12	28	10
MPK0100	56826501	1" conduit size cutter	1"	1.36	35	10
MPC100	56827501	1" conduit size cup	1"	1.36	35	10
MPK0125	56826601	1 1/4" conduit size cutter	1 1/4"	1.70	43	10
MPC125	56827601	1 1/4" conduit size cup	1 1/4"	1.70	43	10
MPK0150	56826701	1 1/2" conduit size cutter	1 1/2"	1.95	50	10
MPC150	56827701	1 1/2" conduit size cup	1 1/2"	1.95	50	10
MPK0200	56826801	2" conduit cutter	2"	2.42	62	10
MPC200	56827801	2" conduit cup	2"	2.42	62	10
MPK0250	56826901	2 1/2" conduit cutter	2 1/2"	2.92	74	10
MPC250	56828001	2 1/2" conduit cup	2 1/2"	2.92	74	10
MPK0300	56827001	3" conduit cutter	3"	3.55	90	10
MPC300	56828101	3" conduit cup	3"	3.55	90	10
MPK0350	56827101	3 1/2" conduit cutter	3 1/2"	4.04	103	10
MPC350	56828201	3 1/2" conduit cup	3 1/2"	4.04	103	10
MPK0400	56827201	4" conduit cutter	4"	4.54	115	10
MPC400	56828301	4" conduit cup	4"	4.54	115	10
MP02	56825701	Small Die Set 1/2"-2" in case*	1/2"-2"	.89-2.42	23-62	10
MP03	56825801	Large Die Set 2 1/2"-4" in case*	2 1/2" - 4"	2.92-4.54	74-115	10

*(drive unit not included)

MODEL #	STOCK #	DESCRIPTION	CONDUIT & PIPE SIZE	HOLE SIZE ACTUAL "	MM	CAPACITY S.S. GA
MPK050PRO	57174601	Max Punch® Cutter for Stainless Steel 1/2"	1/2"	.89	23	10 reg
MPC50PRO	57176101	Max Punch® Cup for Stainless Steel 1/2"	1/2"	.89	23	10 reg
MPK075PRO	57174701	Max Punch® Cutter for Stainless Steel 3/4"	3/4"	1.12	28	10 reg
MPC75PRO	57176201	Max Punch® Cup for Stainless Steel 3/4"	3/4"	1.12	28	10 reg
MPK0100PRO	57174801	Max Punch® Cutter for Stainless Steel 1"	1"	1.36	35	10 reg
MPC100PRO	57176301	Max Punch® Cup for Stainless Steel 1"	1"	1.36	35	10 reg
MPK0125PRO	57174901	Max Punch® Cutter for Stainless Steel 1 1/4"	1 1/4"	1.70	43	10 reg
MPC125PRO	57176401	Max Punch® Cup for Stainless Steel 1 1/4"	1 1/4"	1.70	43	10 reg
MPK0150PRO	57175001	Max Punch® Cutter for Stainless Steel 1 1/2"	1 1/2"	1.95	50	10 reg
MPC150PRO	57176501	Max Punch® Cup for Stainless Steel 1 1/2"	1 1/2"	1.95	50	10 reg
MPK0200PRO	57175101	Max Punch® Cutter for Stainless Steel 2"	2"	2.42	62	10 reg
MPC200PRO	57176601	Max Punch® Cup for Stainless Steel 2"	2"	2.42	62	10 reg
MPK0250PRO	57175301	Max Punch® Cutter for Stainless Steel 2 1/2"	2 1/2"	2.92	74	10 reg
MPC250PRO	57176701	Max Punch® Cup for Stainless Steel 2-1/2"	2 1/2"	2.92	74	10 reg
MPK0300PRO	57175401	Max Punch® Cutter for Stainless Steel 3"	3"	3.55	90	10 reg
MPC300PRO	57176801	Max Punch® Cup for Stainless Steel 3"	3"	3.55	90	10 reg
MPK0350PRO	57175501	Max Punch® Cutter for Stainless Steel 3 1/2"	3 1/2"	4.04	103	10 reg
MPC350PRO	57176901	Max Punch® Cup for Stainless Steel 3 1/2"	3 1/2"	4.04	103	10 reg
MPK0400PRO	57175601	Max Punch® Cutter for Stainless Steel 4"	4"	4.54	115	10 reg
MPC400PRO	57177001	Max Punch® Cup for Stainless Steel 4"	4"	4.54	115	10 reg
MP02PRO	57177101	Small Die Set 1/2"-2" in case (drive unit not included)	1/2"-2"	.89-2.42	23-62	10 reg
MP03PRO	57177201	Large Die Set 2 1/2"- 4" in case (drive unit not included)	2 1/2" - 4"	2.92-4.54	74-115	10 reg

Southwire Company
One Southwire Drive
Carrollton, GA 30119



Southwire™



Customer Service: 1-855-SWTOOLS (855-798-6657)

Scan code to see more
Southwire Tools

southwiretools.com