



Cable Cutting Pliers

**SHEAR TYPE HOOK JAWS
GRAB AND HOLD CABLE WHILE
SHEAR CUTTING ACTION MAKES
CLEAN CUTS.**

● **SUPERIOR CUTTING POWER**

heat treated, precision ground blades
ensure clean cuts

● **COMFORTABLE GRIP**

Comfortable cushion grips
reduce hand fatigue

● **PRECISION**

beveled tips
for positive mating

● **HIGH LEVERAGE
PIVOT JOINT**

hot riveted pivot joint
ensures smooth action
and no handle wobble

● **HIGHLY DURABLE**

forged steel with black-oxide finish for long life



Southwire™

Tools & Assembled Products Division

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-SWT00LS
(855-798-6657)



Scan code to see more
Southwiretools.com



Southwire™

CCP6 / CCP9 / CCP9D / CCP350

Cable Cutting Pliers



CCP6

- 6 1/4" COMPACT CABLE CUTTER



CCP9D

- 9" HIGH LEVERAGE CABLE CUTTER
- DIPPED GRIP



CCP9

- 9" HIGH LEVERAGE CABLE CUTTER
- COMFORT GRIP



CCP350

- 16" UTILITY CABLE CUTTER
- CRIMPING
- COMFORT GRIP

MODEL #	CCP6	CCP9	CCP9D	CCP350
STOCK #:	589934	589935	582932	591585
DESCRIPTION:	6 1/2" CABLE CUTTER SHEARS	9" HI LEV CABLE CUTTERS	9" HI LEV CABLE CUTTERS DIP HANDLE	16" UTILITY CABLE CUTTER 350 Cu/Al
HEIGHT:	6.75"	9.38"	9.38"	17"
WIDTH:	2"	2.13"	2.25"	5"
DEPTH:	0.75"	0.63"	0.63"	0.75"
WEIGHT:	8.6 oz	15 oz	15.4 oz	2.8 oz
HANDLE COLOR:	YELLOW/BLK	YELLOW/BLK	YELLOW	YELLOW/BLK
HANDLE FINISH:	COMFORT GRIP	COMFORT GRIP	DIPPED GRIP	COMFORT GRIP
*MAXIMUM CUTTING CAPACITY (COPPER):	1/0 AWG	2/0 AWG	2/0 AWG	350 kcmil(MCM)
*MAXIMUM CUTTING CAPACITY (ALUM.):	1/0 AWG	4/0 AWG	4/0 AWG	351 kcmil(MCM)



Southwire™

Tools & Assembled Products Division

[BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.]

1-855-SWT00LS
(855-798-6657)



Scan code to see more
Southwiretools.com