



**Southwire®**

**CCP6/CCP6D/CCP9/CCP9D/CCP350**

# CABLE CUTTING PLIERS

Curved jaws grab and hold cable while shear cutting blades make clean cuts.

● **SUPERIOR CUTTING POWER**  
Heat treated, precision ground blades

● **COMFORTABLE GRIP**  
Comfortable cushion grips  
reduce hand fatigue

● **HIGH LEVERAGE  
PIVOT JOINT**  
Ensures smooth action  
and no handle wobble

● **HIGHLY DURABLE**  
Forged steel with black-oxide finish for long life



**Southwire™**

TOOLS & EQUIPMENT

[ BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK. ]

**1-855-SWTOOLS**  
**(855-798-6657)**



[Southwiretools.com](http://Southwiretools.com)



### Availability



**CCP6**  
 ● 6 1/2" Compact Cable Cutter



**CCP6D**  
 ● 6 1/2" Compact Cable Cutter  
 ● Dipped Grip



**CCP9**  
 ● 9" High Leverage Cable Cutter  
 ● Comfort Grip



**CCP9D**  
 ● 9" High Leverage Cable Cutter  
 ● Dipped Grip



**CCP350**  
 ● 16" Utility Cable Cutter  
 ● Comfort Grip

### Specifications

MODEL #	CCP6	CCP6D	CCP9	CCP9D	CCP350
STOCK #	589934	587489	589935	582932	591585
DESCRIPTION	6 1/2" Cable Cutter	6 1/2" Cable Cutter Dip Handle	9" High Leverage Cable Cutter	9" High Leverage Cable Cutter Dip Handle	16" Utility Cable Cutter 350 Cu/Al
HEIGHT	0.5"	0.5"	9.38"	9.38"	17"
WIDTH	2"	2"	2.13"	2.25"	5"
DEPTH	0.75"	0.75"	0.63"	0.63"	0.75"
WEIGHT	8.6 oz	8.2 oz	15 oz	15.4 oz	2 lbs 8 oz
HANDLE COLOR	Black/Yellow	Yellow	Black/Yellow	Yellow	Black/Yellow
HANDLE FINISH	Comfort Grip	Dipped Grip	Comfort Grip	Dipped Grip	Comfort Grip
*MAXIMUM CUTTING CAPACITY (COPPER)	1/0 AWG	1/0 AWG	2/0 AWG	2/0 AWG	350 kcmil(MCM)
*MAXIMUM CUTTING CAPACITY (ALUM.)	1/0 AWG	1/0 AWG	4/0 AWG	4/0 AWG	350 kcmil(MCM)

