


PAR46




PAR56




PS25




PS30



BR40



R40



BR38

Watt	Shape	Base	Item No	Description	Volt	Avg Life Hours	Color/Beam Spread	Notes	Ctn Qty
INCANDESCENT BULBS (Cont'd)									
GENERAL SERVICE (Cont'd)									
200	PAR46	Side Prng	01241B	200PAR463MFL	120	2000	Medium Flood		12
			00458D	200PAR463NSP	130	2000	Narrow Spot		12
			00457D	200PAR463MFL	130	2000	Medium Flood		12
	PAR56	G16d Screw	05451D	200PAR56MFL	120	2000	Medium Flood		6
			05466D	200PAR56	30	350	Clear		6
	PS25	Medium	01041A	200PS25CLRS	130	4000	Clear	Rough Service	60
			00456A	200PS25/RS	130	4000	Inside Frost	Rough Service	60
			00459A	200PS25/IF/RS/SS	130	4000	Inside Frost	Safe-Shield® Coated, Rough Service	60
		E27	05715A	200PS25CL	230	1000	Clear		60
			05362B	200PS25CL	250	1000	Clear		60
			05362C	200PS25/OF	250	1000	Clear		60
			05819A	200PS25CL/SS	250	1000	Clear	Safe-Shield® Coated	60
			05547B	200PS25CL	277	1000	Clear		60
			05547C	200PS25CL/SS	277	1000	Clear	Safe-Shield® Coated	60
			06397A	200PS25CL	300	1000	Clear		60
	PS30	Medium	00442D	200PS3099CL	130	4000	Clear		60
			20433A	200PS3099IF	130	4000	Inside Frost		60
			02762A	200PS3099CL/SS	130	4000	Clear	Safe-Shield® Coated	60
			00442F	200PS3099IF/SS	130	4000	Inside Frost	Safe-Shield® Coated	60
		Mogul	00460D	200PS30/12	130	4000	Clear		60
01756A			200PS3012/IF	130	4000	Inside Frost		60	
00450B			200PS3099SBIF	130	4000	Silver Bowl	Inside Frost	60	
01756C			200PS3012/IF/SS	130	4000	Inside Frost	Safe-Shield® Coated	60	
E40	05715B	200PS30CL	230	1000	Clear		60		
250	BR40	Medium	00465D	250BR40/1	130	5000	Clear		24
			01520A	250BR40/1/SSFC	130	5000	Clear	High Temp Safe-Shield® Coated	24
	R40	Medium	00466D	250R40/10	130	5000	Red		24
300	BR38	Medium	21113A	300BR38FL	130	4000	Flood		24
			22242A	300BR38FL/SSFC	130	4000	Flood	High Temp Safe-Shield® Coated	24
	BR40	E27	21277A	300BR40FL	277	2000	Flood		24
	PAR56	G16d	00487D	300PAR56NSP	120	2000	Narrow Spot		12
			00485D	300PAR56MFL	120	2000	Medium Flood		12
			00490E	300PAR56WFL	120	2000	Wide Flood		12
			00488D	300PAR56NSP	130	2000	Narrow Spot		12
			00486D	300PAR56MFL	130	2000	Medium Flood		12
			00489D	300PAR56WFL	130	2000	Wide Flood		12
	PS25	Medium	00480A	300M99	130	4000	Clear		60
00482B			300MPS2599IF	130	4000	Inside Frost		60	
20165A			300M99PS25CL/SS	130	4000	Clear	Safe-Shield® Coated	60	
02554B			300MPS2599IF/SS	130	4000	Inside Frost	Safe-Shield® Coated	60	
02554A			300MPS2599IF/SSFC	130	4000	Inside Frost	High Temp Safe-Shield® Coated	60	
PS30	Medium	04098B	300M99PS30CL	130	4000	Clear		60	
		01242B	300MPS30IF	130	4000	Inside Frost		60	

Click Below To Order

Interlight Specialty Bulbs
1-800-743-0005
www.interlight.biz