

	Intellinet Part #	Description	Managed	Housing	Standard	Integrated Fans	PoE Ports	Power Budget
<p>Shown: 524179</p> 	524179	1-Port Fast Ethernet PoE Injector	No	Desktop	IEEE 802.3af	—	1	15.4 W
	560566	1-Port Gigabit High-Power PoE+ Injector	No	Metal; Desktop	IEEE 802.3af/at	—	1	30 W
	561037	1-Port Gigabit High-Power PoE+ Injector	No	Plastic; Desktop	IEEE 802.3af/at	—	1	30 W
	561235	1-Port Gigabit Ultra PoE+ Injector	No	Plastic; Desktop	IEEE 802.3af/at	—	1	60 W
	560443	Power over Ethernet (PoE+) Splitter	No	Desktop	IEEE 802.3af/at	—	1	—
	560962	1-Port Gigabit High-Power PoE+ Extender Repeater	No	Desktop	IEEE 802.3af/at	—	1	24.6 W
<p>Shown: 561082</p> 	561082	PoE-Powered 5-Port Gigabit Switch with PoE Passthrough	No	Desktop	IEEE 802.3af/at	—	5	68 W with AC power; 26 W with PD input port
	561174	5-Port Gigabit Ethernet PoE+ Switch with SFP Combo Port	No	Desktop	IEEE 802.3af/at	—	4	80 W
<p>Shown: 560641</p> 	561075	8-Port Fast Ethernet PoE+ Switch (4 x 4)	No	Desktop & Rackmount	IEEE 802.3af/at	—	4	70 W
	560764	8-Port Fast Ethernet PoE+ Switch	No	Desktop	IEEE 802.3af/at	—	8	140 W
	560641	8-Port Gigabit Ethernet PoE+ Switch	No	Desktop & Rackmount	IEEE 802.3af/at	—	8	140 W
	561204	8-Port Gigabit Ethernet PoE+ Switch	No	Desktop	IEEE 802.3af/at	—	8	60 W
	561358	8-Port Fast Ethernet PoE+ Web-Smart Switch with 1 Gigabit Combo Port	Yes	Desktop & Rackmount	IEEE 802.3af/at	—	8	130 W
	561167	8-Port Gigabit Ethernet PoE+ Web-Managed Switch with 2 SFP Ports	Yes	Desktop & Rackmount	IEEE 802.3af/at	1	8	140 W
<p>Shown: 560993</p> 	560771	16-Port Fast Ethernet PoE+ Switch (8 x 8)	No	Rackmount	IEEE 802.3af/at	1	8	58 W
	560849	16-Port Fast Ethernet PoE+ Switch	No	Rackmount	IEEE 802.3af/at	1	16	250 W
	560993	16-Port Gigabit Ethernet PoE+ Switch	No	Rackmount	IEEE 802.3af/at	1	16	220 W
	561341	16-Port Gigabit Ethernet PoE+ Web-Managed Switch with 2 SFP Ports	Yes	Rackmount	IEEE 802.3af/at	2	16	220 W
	NEW 561198	16-Port Gigabit Ethernet PoE+ Web-Managed Switch with 2 SFP Ports	Yes	Rackmount	IEEE 802.3af/at	2	16	374 W
<p>Shown: 560559</p> 	560559	24-Port Gigabit Ethernet PoE+ Web-Managed Switch with 2 SFP Ports	Yes	Rackmount	IEEE 802.3af/at	2	24	240 W
	561143	24-Port Gigabit Ethernet PoE+ Switch with 10 GbE Uplink	No	Rackmount	IEEE 802.3af/at	2	24	400 W
	561372	24-Port Gigabit Ethernet PoE+ Web-Managed Switch with 4 SFP Combo Ports	Yes	Rackmount	IEEE 802.3af/at	2	24	430 W
	561105	24-Port Gigabit Ethernet PoE+ Layer2+ Managed Switch with 4 10 GbE Uplinks	Yes	Rackmount	IEEE 802.3af/at	2	24	420 W
	561112	48-Port Gigabit Ethernet PoE+ Layer2+ Managed Switch with 2 10 GbE Uplinks	Yes	Rackmount	IEEE 802.3af/at	2	48	400 W