


# 4550 Cross Arm Strap Technical Data Sheet



## Cross Arm Strap

Has a minimum tensile breaking strength of 5,000 pounds (22.2 kN) when statically tested in accordance with the requirements of the ANSI Z359.1-2007 standard.



Part Number 3M ID	Material	Length	Connection Material	Connection Opening	Weight	Compliance Standards
4550 70071532405	2 in Polyester Webbing	6 ft (1.8 m)	Stamped Steel D-ring	2 x 1¼ in (51 x 44 mm)	1 lb (454 g)	ANSI Z359.1-07
4550-3 70071525870	2 in Polyester Webbing	3 ft (0.9 m)	Stamped Steel D-ring	2 x 1¼ in (51 x 44 mm)	0.8 lb (363 g)	ANSI Z359.1-07

Weights and measurements are approximate.

## Product Warranty, Limited Remedy, and Limitation of Liability

**WARRANTY:** THE FOLLOWING IS MADE IN LIEU OF ALL WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OR CONDITIONS OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Equipment offered by 3M is warranted against factory defects in workmanship and materials for a period of one year from date of installation or first use by the original owner.

**LIMITED REMEDY:** Upon notice in writing, 3M will repair or replace all defective items at 3M's sole discretion. 3M reserves the right to require that the defective item be returned to its plant for inspection before determining the appropriate course of action. Warranty does not cover equipment damage resulting from wear, abuse, damage in transit, failure to maintain the product or other damage beyond the control of 3M. 3M shall be the sole judge of product condition and warranty options. This warranty applies only to original purchaser and is the only warranty applicable to this product. Please contact 3M technical service department at 800-243-4630 for assistance.

**LIMITATION OF LIABILITY:** IN NO EVENT WILL 3M BE LIABLE FOR ANY INDIRECT, INCIDENTAL, SPECIAL OR CONSEQUENTIAL DAMAGES INCLUDING, BUT NOT LIMITED TO LOSS OF PROFITS, IN ANY WAY RELATED TO THE PRODUCTS REGARDLESS OF THE LEGAL THEORY ASSERTED.

### **⚠ WARNING**

Compliant fall protection and emergency rescue systems help prevent serious injury during fall arrest. Users must read and understand the User Instructions provided with the product and be properly trained by their employer prior to use per OSHA 29 CFR 1910.66 and 1926.503 or applicable local standards. **Misuse or failure to follow warnings and instructions may result in serious personal injury or death.** For proper use, see supervisor, User Instructions, or call Technical Service at 800-243-4630.

## 3M Occupational Health & Environmental Safety Division

3M Center Building 235-2W-70  
Saint Paul, MN 55144-1000  
USA

Technical Assistance: 800-243-4630 in U.S.  
800-267-4414 in Canada  
[www.3M.com/FallProtection](http://www.3M.com/FallProtection)  
[www.3M.com/PPESafety](http://www.3M.com/PPESafety)



Please recycle.  
© 3M 2012  
3M is a trademark of 3M Company,  
used under license in Canada.  
All rights reserved.  
TS-00079 Rev A (10-2012)

