

Transformers

Open Core and Coil Transformers

Control

Single-Phase

Section 14

60 Hz Terminal Board Connection

Input Voltage	Output Voltage	KVA	Frame Size	Wiring Diagram No. ²	Product Number	List Price GO-80
240 x 480 Volts	120/240 Volts	0.05	6100	4	9T58K2802	\$36.00
240 x 480 Volts	120/240 Volts	0.075	6125	4	9T58K2803	\$42.00
240 x 480 Volts	120/240 Volts	0.1	8100	4	9T58K2804	\$45.00
240 x 480 Volts	120/240 Volts	0.15	8150	4	9T58K2805	\$57.50
240 x 480 Volts	120/240 Volts	0.2	8175	4	9T58K2806	\$65.00
240 x 480 Volts	120/240 Volts	0.25	8200	4	9T58K2807	\$73.00
240 x 480 Volts	120/240 Volts	0.3	8200	4	9T58K2808	\$76.00
240 x 480 Volts	120/240 Volts	0.375	8250	4	9T58K2809	\$96.00
240 x 480 Volts	120/240 Volts	0.5	10225	4	9T58K2810	\$104.00
240 x 480 Volts	120/240 Volts	0.75	12225	4	9T58K2811	\$128.00
240 x 480 Volts	120/240 Volts	1	12300	4	9T58K2812	\$164.00
240 x 480 Volts	120/240 Volts	1.5	14225	4	9T58K2813	\$215.00
240 x 480 Volts	120/240 Volts	2	14300	4	9T58K2814	\$274.00
240 x 480 Volts	120/240 Volts	3	14475	4	9T58K2815	\$360.00
600 Volts	120/240 Volts	0.1	8100	5	9T58K2824	\$45.00
600 Volts	120/240 Volts	0.2	8175	5	9T58K2826	\$65.00
600 Volts	120/240 Volts	0.3	8200	5	9T58K2828	\$73.00
600 Volts	120/240 Volts	0.5	10225	5	9T58K2830	\$104.00
600 Volts	120/240 Volts	1	12300	5	9T58K2832	\$194.00
600 Volts	120/240 Volts	2	14300	5	9T58K2834	\$306.00
600 Volts	120/240 Volts	3	14475	5	9T58K2835	\$398.00
120 x 240 Volts	120/240 Volts	0.1	8100	6	9T58K2907	\$44.00
120 x 240 Volts	120/240 Volts	0.2	8175	6	9T58K2909	\$65.50
120 x 240 Volts	120/240 Volts	0.3	8200	6	9T58K2911	\$72.00
120 x 240 Volts	120/240 Volts	0.5	10225	6	9T58K2913	\$101.00
120 x 240 Volts	120/240 Volts	0.75	12225	6	9T58K2914	\$121.00
120 x 240 Volts	120/240 Volts	1	12300	6	9T58K2915	\$155.00
120 x 240 Volts	120/240 Volts	2	14300	6	9T58K2917	\$261.00
120 x 240 Volts	120/240 Volts	3	14475	6	9T58K2918	\$344.00

60 Hz Terminal Board Connection

Input Voltage	Output Voltage	KVA	Frame Size	Wiring Diagram No. ²	Product Number	List Price GO-80
120 x 240 Volts	12/24 Volts	0.05	6100	7	9T58K2873	\$29.00
120 x 240 Volts	12/24 Volts	0.075	6125	7	9T58K2874	\$35.00
120 x 240 Volts	12/24 Volts	0.1	8100	7	9T58K2875	\$39.00
120 x 240 Volts	12/24 Volts	0.15	8150	7	9T58K2876	\$48.50
120 x 240 Volts	12/24 Volts	0.2	8175	7	9T58K2877	\$58.50
120 x 240 Volts	12/24 Volts	0.25	8200	7	9T58K2878	\$62.50
120 x 240 Volts	12/24 Volts	0.3	8200	7	9T58K2879	\$67.00
240 x 480 Volts	12/24 Volts	0.05	6100	—	9T58K3164	\$34.50
240 x 480 Volts	12/24 Volts	0.1	8100	—	9T58K4132	\$40.50
240 x 480 Volts	12/24 Volts	0.15	8150	—	9T58K4133	\$48.50
240 x 480 Volts	12/24 Volts	0.25	8200	—	9T58K3024	\$62.50
208 x 240 Volts	12/24 Volts	0.05	6100	—	9T58K4050	\$34.50
208 x 240 Volts	12/24 Volts	0.1	8100	—	9T58K4051	\$40.50
208 x 240 Volts	12/24 Volts	0.15	8150	—	9T58K4052	\$48.50
208 x 240 Volts	12/24 Volts	0.25	8200	—	9T58K4053	\$62.50

60 Hz Leads Out Connection¹

Input Voltage	Output Voltage	KVA	Frame Size	Wiring Diagram No. ²	Product Number	List Price GO-80
240 x 480 Volts	120/240 Volts	0.05	6100	4	9T58K1802	\$36.00
240 x 480 Volts	120/240 Volts	0.075	6125	4	9T58K1803	\$42.00
240 x 480 Volts	120/240 Volts	0.1	8100	4	9T58K1804	\$45.00
240 x 480 Volts	120/240 Volts	0.15	8150	4	9T58K1805	\$57.50
240 x 480 Volts	120/240 Volts	0.2	8175	4	9T58K1806	\$65.00
240 x 480 Volts	120/240 Volts	0.25	8200	4	9T58K1807	\$73.00
240 x 480 Volts	120/240 Volts	0.3	8200	4	9T58K1808	\$76.00
240 x 480 Volts	120/240 Volts	0.375	8250	4	9T58K1809	\$96.00
240 x 480 Volts	120/240 Volts	0.5	10225	4	9T58K1810	\$104.00
240 x 480 Volts	120/240 Volts	0.75	12225	4	9T58K1811	\$128.00
240 x 480 Volts	120/240 Volts	1	12300	4	9T58K1812	\$164.00
240 x 480 Volts	120/240 Volts	1.5	14225	4	9T58K1813	\$215.00
240 x 480 Volts	120/240 Volts	2	14300	4	9T58K1814	\$274.00
240 x 480 Volts	120/240 Volts	3	14475	4	9T58K1815	\$360.00

¹Secondary fusing not available.

²See page 14-6 for wiring diagrams.

