

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K0088	9T58R0088	1	50	CU	0.30	208/277/380	115/95	80	40	10225	NONE	Screw Terminals
9T58K0089	9T58R0089	1	50	CU	0.38	208/277/380	115/95	80	40	10225	NONE	Screw Terminals
9T58K0090	9T58R0090	1	50	CU	0.50	208/277/380	115/95	115	40	10225	NONE	Screw Terminals
9T58K0091	9T58R0091	1	50	CU	0.75	208/277/380	115/95	80	40	12300	NONE	Screw Terminals
9T58K0092	9T58R0092	1	50	CU	1.00	208/277/380	115/95	100	40	14225	NONE	Screw Terminals
9T58K0093	9T58R0093	1	50	CU	1.50	208/277/380	115/95	100	40	14300	NONE	Screw Terminals
9T58K0094	9T58R0094	1	50	CU	2.00	208/277/380	115/95	100	40	14475	NONE	Screw Terminals
9T58K0095	9T58R0095	1	60	CU	3.00	208/277	115	115	40	14475	NONE	Screw Terminals
9T58K0727	9T58R0727	1	50	CU	0.10	400	120	55	40	8150	NONE	Screw Terminals
9T58K0728	9T58R0728	1	50	CU	0.25	380/415/480	120	100	40	8250	NONE	Screw Terminals
9T58K0945	9T58R0945	1	50	CU	0.50	380/415/480	120	100	40	12225	NONE	Screw Terminals
9T58K0946	9T58R0946	1	50	CU	0.50	230	208	115	40	10225	NONE	Screw Terminals
9T58K0947	9T58R0947	1	50	CU	0.50	600	208	115	40	10225	NONE	Screw Terminals
9T58K0948	9T58R0948	1	50	CU	1.00	230	208	115	40	12300	NONE	Screw Terminals
9T58K0949	9T58R0949	1	50	CU	1.00	480	208	115	40	12300	NONE	Screw Terminals
9T58K0950	9T58R0950	1	50	CU	1.00	600	208	115	40	12300	NONE	Screw Terminals
9T58K1000	9T58R1000	1	60	CU	0.75	120x240	75	100	40	12225	NONE	Screw Terminals
9T58K1012	9T58R1012	1	60	CU	1.00	480	220	100	40	12300	NONE	Screw Terminals
9T58K1015	9T58R1015	1	60	CU	3.00	480	220	100	40	14475	NONE	Screw Terminals
9T58K1101	9T58R1101	1	50	CU	0.10	415	110	55	40	8150	NONE	Screw Terminals
9T58K1692	9T58R1692	1	50	CU	1.65	330	158	115	40	12300	NONE	Screw Terminals
9T58K1695	9T58R1695	1	60	CU	0.15	277	12/24	55	40	8150	NONE	Screw Terminals
9T58K1696	9T58R1696	1	50	CU	1.20	240	105	115	40	12300	NONE	Screw Terminals
9T58K1697	9T58R1697	1	50	CU	0.87	330	158	115	40	10225	NONE	Screw Terminals
9T58K1698	9T58R1698	1	60	CU	1.50	120	90	100	40	14225	NONE	Screw Terminals
9T58K2802	9T58R2802	1	60	CU	0.05	240x480	120/240	55	40	6100	NONE	Screw Terminals
9T58K2803	9T58R2803	1	60	CU	0.08	240x480	120/240	55	40	6125	NONE	Screw Terminals
9T58K2804	9T58R2804	1	60	CU	0.10	240x480	120/240	55	40	8100	NONE	Screw Terminals
9T58K2805	9T58R2805	1	60	CU	0.15	240x480	120/240	55	40	8150	NONE	Screw Terminals
9T58K2806	9T58R2806	1	60	CU	0.20	240x480	120/240	80	40	8175	NONE	Screw Terminals
9T58K2807	9T58R2807	1	60	CU	0.25	240x480	120/240	80	40	8200	NONE	Screw Terminals
9T58K2808	9T58R2808	1	60	CU	0.30	240x480	120/240	100	40	8200	NONE	Screw Terminals
9T58K2809	9T58R2809	1	60	CU	0.38	240x480	120/240	100	40	8250	NONE	Screw Terminals
9T58K2810	9T58R2810	1	60	CU	0.50	240x480	120/240	100	40	10225	NONE	Screw Terminals
9T58K2811	9T58R2811	1	60	CU	0.75	240x480	120/240	100	40	12225	NONE	Screw Terminals
9T58K2812	9T58R2812	1	60	CU	1.00	240x480	120/240	100	40	12300	NONE	Screw Terminals