

Ordering codes for XT3 UL/CSA Accessories



EF terminal



FCCuAl terminal

Terminals

Type	3 pcs Part number	4 pcs Part number	6 pcs Part number	8 pcs Part number
F Front terminals	KXT3F-3PC	KXT3F-4PC	KXT3F-6PC	KXT3F-8PC
EF Extended front terminals	KXT3EF-3PC	KXT3EF-4PC	KXT3EF-6PC	KXT3EF-8PC
ES Extended spread terminals	KXT3ES-3PC	KXT3ES-4PC	KXT3ES-6PC	KXT3ES-8PC
FC CuAl Terminals for CuAl cables 100A, 14-1/0 AWG, 1x2.5...50mm ⁽¹⁾	KXT3CUAL1-3PC	KXT3CUAL1-4PC	KXT3CUAL1-6PC	KXT3CUAL1-8PC
FC CuAl Terminals for CuAl cables w/Control Tap 100A, 14-1/0 AWG, 1x2.5...50mm ⁽¹⁾	KXT3CUAL1C-3PC	KXT3CUAL1C-4PC	-	-
FC CuAl Terminals for CuAl cables 225A, 4 AWG -300 kcmil, 1x35...150mm ⁽¹⁾	KXT3CUAL2-3PC	KXT3CUAL2-4PC	KXT3CUAL2-6PC	KXT3CUAL2-8PC
FC CuAl Terminals for CuAl cables w/Control Tap 225A, 4 AWG -300 kcmil, 1x35...150mm ⁽¹⁾	KXT3CUAL2C-3PC	KXT3CUAL2C-4PC	-	-
FC Cu Terminals for Cu cables, 10-250 AWG, 1x6...185mm ²	KXT3CU-3PC	KXT3CU-4PC	KXT3CU-6PC	KXT3CU-8PC
MC Multi cable terminals for Cu cables, 6x12-2 AWG, 6x2.5...35mm ²	KXT3MC-3PC	KXT3MC-4PC	KXT3MC-6PC	KXT3MC-8PC
R Rear adjustable terminals ⁽²⁾	KXT3ER-3PC	KXT3ER-4PC	KXT3ER-6PC	KXT3ER-8PC
R-RC Rear terminal for residual current ⁽²⁾	-	KXT3ERRC-4PC	-	-
FB Flexibar terminals ⁽²⁾	KXT3EFB-3PC	KXT3EFB-4PC	KXT3EFB-6PC	KXT3EFB-8PC

⁽¹⁾Consult ABB for availability.

⁽²⁾IEC rated only.

Automatic transfer devices

ATS021 - ATS022 automatic transfer devices⁽¹⁾

Type	Part number			
ATS021	ATS021			
ATS022	ATS022			

⁽¹⁾IEC rated only.

Spare parts

Type	Fixed/Plugin-in Part number			
SA RC Sel/RC B Type - opening solenoid for the residual current device ⁽¹⁾	KXT3ESARCFP			
SA RC B Type - Opening solenoid for the residual current device ⁽¹⁾	KXT3ESARCFPB			
AUX-C - Loose cabled auxiliary contact 250V AC ⁽²⁾	KXTAAUXCFP			
AUX-C - Loose cabled auxiliary contact 24V DC ⁽²⁾	KXTAAUXCDFP			
AUX-C - Loose cabled auxiliary contact 250V AC HD for 600V	KXTAAUXCFPHD			
AUX-C - Loose cabled auxiliary contact 24V DC HD for 600V	KXTAAUXCDFPHD			

⁽¹⁾IEC rated only

⁽²⁾Un-numbered cables

Flanges for the compartment door

Type	3p Part number	4p Part number		
Small "optional" flange for circuit breaker	KXTAEFLASMFP	KXTAEFLASMFP		
Large "standard" flange for circuit breaker	KXT3EFLAFP-3	KXT3EFLAFP-4		
Flange for MOD	KXTBEFLAMOD	KXTBEFLAMOD		
Flange for direct handle RHD	KXTAEFLARHDFP	KXTAEFLARHDFP		
Flange for residual current RC Sel / Inst	KXT3EFLARCFP-3	KXT3EFLARCFP-4		

⁽¹⁾IEC rated only.



Flange