








Blank Markers

Photo	For Use With	Markers per Card	Marker Size	Pkg Qty.	Cat. No.
<p>Snap-In Individual Markers 1492-M</p>   	1492-L	100	3 x 5 mm	5	1492-M3X5
	1492-L	120	3 x 12 mm	5	1492-M3X12
	1492-J, L	200	5 x 5 mm	5	1492-M5X5
		144	5 x 8 mm	5	1492-M5X8
		144	5 x 10 mm	5	1492-M5X10
		144	5 x 12 mm	5	1492-M5X12
		96	5 x 15 mm	5	1492-M5X15
		20	5 x 30 mm	5	* 1492-M5X30
	1492-J, L	200	6 x 5 mm	5	1492-M6X5
	120	6 x 10 mm	5	1492-M6X10	
	1492-J, L, 1738 ArmorPoint™	120	6 x 12 mm	5	1492-M6X12
	1492-J, L	108	7 x 12 mm	5	1492-M7X12
		160	8 x 5 mm	5	1492-M8X5
	NEMA (1492-HM1, -HM2, -HM3) Terminal Blocks, 1492-CB Circuit Breakers	120	6 x 10 mm	5	1492-MN81
	NEMA (1492-HM3) Terminal Blocks, 1492-CB Circuit Breakers	40	10 x 10 mm	5	1492-MN83
	1492-W,R, 700-HA Relays	56	8 x 9 mm	5	1492-MS8X9
56		8 x 12 mm	5	1492-MS8X12	
700-HN204, -HN205, Relay Sockets	40	8 x 17 mm	5	1492-MS8X17	
1667 PanelConnect™	40	9 x 20 mm	5	1492-MS9X20	
100-C, -D Contactors, 700-CF Relays, 140 Circuit Breakers, 193-E1, -E3	40	10 x 17 mm	5	1492-MS10X17	
<p>Snap-In Linked Markers 1492-MR</p> 	1492-J, -L	120	5 x 8 mm	5	1492-MR5X8
		120	6 x 8 mm	5	1492-MR6X8
		120	5 x 12 mm	5	1492-MR5X12
		120	6 x 12 mm	5	1492-MR6X12
		84	8 x 12 mm	5	1492-MR8X12
			1492-WM3, -WMD1	80	5 x 5 mm
1492-W, 700-HA, 800F Contact Block	80		5 x 9 mm	5	1492-MS5X9
1492-W, 700-H Relays	80		5 x 12 mm	5	1492-MS5X12
1492-W, -R, 700-H Relays	80		6 x 9 mm	5	1492-MS6X9
1492-W, 700-H Relays	80		6 x 12 mm	5	1492-MS6X12
<p>Snap-In Hinged Markers</p> 	1492-L	96	5 x 10 mm	5	1492-MH5X10
		96	5 x 15 mm	5	1492-MH5X15
		80	6 x 12 mm	5	1492-MH6X12
<p>Cable Markers 1492-MW</p> 	External Diameter (mm)	Markers per Card	Marker Size	Pkg. Qty.	Cat. No.
	from 0.276 in. (from 7.0 mm)	32	9 x 24 mm*	5	1492-MW9X24
	from 0.276 in. (from 7.0 mm)	32	5 x 23 mm*	5	1492-MW10X23
	from 0.276 in. (from 7.0 mm)	32	8 x 23 mm*	5	1492-MW14X23
	from 0.276 in. (from 7.0 mm)	12	11 x 44 mm*	5	1492-MW11X60
	0.162...0.193 in. (4.1...4.9 mm)	32	5 x 21 mm‡	5	1492-MW5-21
	0.185...0.229 (0.268) in. (4.7...5.8 [6.8] mm)	32	6 x 21 mm‡	5	1492-MW6-21
	0.229...0.276 (0.335) in. (5.8...7.0 [8.5] mm)	32	7 x 21 mm‡	5	1492-MW7-21

* Requires cable ties.

* Requires Cat. No. 1492-GMC

‡ Requires Cat. No. 1492-PLOTPLTA