

Catalog Number
Notes
Type

FEATURES & SPECIFICATIONS

INTENDED USE

These fixtures provide an attractive low-cost lighting solution in residential and light commercial applications. Ideal for use in entryways, hallways, bedrooms, offices, utility work areas, stairways and many other rooms. Provides general illumination in residential applications.

CONSTRUCTION

Deco-styled fixture with choice of white, polished brushed nickel or bronze housing and matching decorative center finial. Softly rounded molded, white glass diffuser for a widespread, uniform illumination. Center finial provides easy access for cleaning and maintenance.

OPTICS

Includes (1) 55W 2C T6 2700K fluorescent lamp for energy efficiency, superior color rendering and long life.

ELECTRICAL

Standard with electronic ballast (120 volt, 60HZ) ensures no flickering and quiet operation without interfering with other home electronics.

INSTALLATION

All mounting hardware included.

LISTINGS

UL listed to US and Canadian safety standards and suitable for damp locations.

WARRANTY

1-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

NOTE: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25°C. Specifications subject to change without notice.

Indoor Decorative


Décor Round Flush Mount



ESSENTIAL SERIES
2C T6 Fluorescent



DIMENSIONS					
Nominal size	Lamp configuration	Model number	Number of lamps	(A) Width inches (cm)	(B) Extension* inches (cm)
15" dia		11983 BNP	(1) 55W 2C T6	15 (38.1)	5-1/2 (14.0)
*Extension from ceiling. All dimensions are inches (centimeters) unless otherwise indicated.					



ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

Example: 11983 BNP

11983		Model number ^{1,2}		Finish		Ballast/Voltage ²	
11983	15" diameter - (1) 55W 2C T6 2700K fluorescent lamp (Included)	BNP	Polished brushed nickel	WH	White	(blank)	120V residential electronic ballasts (standard)
		BZ	Bronze				

Replacement parts: Order as separate catalog number.

F2CS527 R6	55W 2C T5 2700K fluorescent lamp
DDECR15	Glass diffuser, white

Notes

- INCLUDES - (1) 55W 2C T6 2700K fluorescent lamp.
- Use with non-dimmable switches only.

Décor Round Flush Mount

PHOTOMETRICS

Full photometric data report available within 2 weeks from request. Consult factory.