





ACCESSORIES




order separately

HANGING DEVICES

	TYPE	DESCRIPTION	LENGTH	AVAILABILITY	DESIGNATION		
	Stem Hangers Length measured from ceiling plane to middle of threads. Adjusts 1" up or down. Offset bar on SQ and Q swivels 30° from vertical in any direction.	Complete assembly with stem, canopy, offset bar and parts. (Canopy adds 1" to overall length. EX: SQ8=9")	8"	All commercials, industrial and strips (available in 2" increments)	SQ8		
			12"		SQ12		
			18"		SQ18		
			24"		SQ24		
			8"		ST8		
			12"		ST12		
			18"		ST18		
			24"		ST24		
			36"		ST36		
			48"		ST48		
60"	ST60						
	Double-stem canopy (specify stem length)	Double-stem canopy for use with ST stems (stems on 10" centers)	48"	Most 4' industrials, strips & commercials except M series fixtures.	ST48TBE		
					Canopy, offset bar and parts	Q	
						2__	
	Hooker™ Hangers To secure surface mounted fixtures to inverted T ceilings. 2 per channel required.	Mounts fixture flush to ceiling	1-1/2" from ceiling	CB,L,LA and C Series (4-3/16" wide channel)	HRC		
						HRC1	
					Mounts fixture flush to ceiling	PV,AF,SL,EJ and UN Series (5" wide channel)	HRUN
					Mounts fixture 1-1/2" from ceiling		HRUN1
Ceiling Spacers	Short stem and canopy 2 per fixture required.	Adjustable 1-1/2"-2-1/2" from ceiling.		All commercials, industrials and strips	1B		
	Tong Hangers Hangers clamp on to top of fixture channel. Order as shown by channel width and diameter of hole for stem or rod.	For 5/8" stem For 1/4" rod For 3/8" rod	For 5/8" stem For 1/4" rod For 3/8" rod	Fixtures using 5" wide UN channel. Fixtures using 9" wide UN channel	102B1		
						102B2	
						102B3	
						103B1	
						103B2	
						103B3	
						106B1	
						106B2	
						106B3	

HANGING DEVICES

ACCESSORIES
order separately

	TYPE	DESCRIPTION	LENGTH	AVAILABILITY	DESIGNATION
	Chain Hangers	Two wire hangers and two 36" chains (contact factory for other lengths)	Chain Hanger	Fixtures using 5" wide UN channels or 4-3/16" C channels DL, DV and DD series (hanger bracket required)	HC
		Use two per fixture in both unit and row installation			
	Hanger Brackets	Brackets to secure HC accessory to damp and wet location fixtures. One pair furnished. (Note: bracket required for HC installation on DL, DV or DD fixtures)	Hanger Bracket	DL Series	BCL
				DV Series	BCV
				DD Series	BCD
	Yokes	Devices to span ceiling opening and support fixture. Specific ceiling design must be known; consult factory for mounting details. One pair supplied (one pair per fixture required).	Yokes for 1'x4' fixture	SPF Series	YF
			Yokes for 2'x2' or 2'x4' fixture		2YF

For more information, contact Lithonia Fluorescent Applications Engineering.

Revised 12/8