

Bulletin 700-HF Square Base Relay

Introduction

Standards Compliance and Certifications

Product Selection


Accessories

Specifications

Approximate Dimensions












Accessories

	Description	Pkg. Quantity	Cat. No.
	Pre-Printed Identification Tags – contains 10 sheets of pre-printed and blank tags. Each sheet contains 13 sets of the markings CR...9CR, TR...9TR, M...9M, F, R, 1S, and 117 blank tags. Tags are peel-off with sticky backing for easy placement on relays.	10	700-N40
	Blank Identification Tags – contains 10 sheets of blank identification tags for customer specialized printing. Each sheet contains 546 blank tags. Tags are peel-off with sticky backing for easy placement on relays.	10	700-N41

* Performance Data - See this catalog, Important-Performance Data.

‡ For pre-printed marker cards, turn to the following 1492 sections of this publication: 1492-MS5X12_, 1492-MS6X9_, 1492-MS8X9_, 1492-MS8X12_, 1492-MP_.

	Description	Pkg. Qty.	Cat. No.
 Cat. No. 700-HN116	Screw Terminal Socket – Panel or DIN Rail Mounting 8-blade miniature socket for use with DPDT HF relays.	10	700-HN116
 Cat. No. 700-HN262	Screw Terminal Socket – Panel or DIN Rail Mounting, Guarded Terminal Construction 8-blade socket for use with DPDT Bulletin 700-HF relays. The socket has the ability to use optional plug-in modules (Cat. No. 700-A_ _ accessories, LED, surge suppression, timing modules).	10	700-HN262
 Cat. No. 700-HN139	Screw Terminal Socket – Panel or DIN Rail Mounting, Guarded Terminal Construction 14-blade socket for use with 4PDT Bulletin 700-HF relays.	10	700-HN139
	Screw Terminal Socket – Panel or DIN Rail Mounting, Guarded Terminal Construction 14-blade socket for use with 4PDT Bulletin 700-HF relays. The socket has coil and contact separation and the ability to use optional plug-in modules (Cat. No. 700-A_ _ accessories, LED, surge suppression, timing modules).	10	700-HN264

 <p>Cat. No 199-DR1</p>	<p>DIN (#3) symmetrical hat rail 35 x 7.5 x 1 m</p>	10	199-DR1	
 <p>Sample Retainer Clips</p>	<p>Retainer Clip for Cat. Nos. 700-HN103, -HN104 and -HN128 Sockets with 700-HC Relays and Cat. Nos. 700-HN116, 700-HN262 Sockets with Bulletin 700-HF DPDT Relays Secures relay in socket. Order must be for 10 clips or multiples of 10.</p>	10	700-HN114	
	<p>Retainer Clip for Cat. Nos. 700-HN139 and -HN264 Sockets with Bulletin 700-HF 4PDT Relays Secures relay in socket. Order must be for 10 clips or multiples of 10.</p>	10	700-HN266	
	<p>Diode with LED Surge Suppressor Voltage Range: 6...24V DC used with sockets that accept plug-in accessory modules.</p>	10	700-ADL1	
	<p>Diode with LED Surge Suppressor Voltage Range: 28...60V DC used with sockets that accept plug-in accessory modules.</p>	10	700-ADL2	
	<p>Diode with LED Surge Suppressor Voltage Range: 110...220V DC used with sockets that accept plug-in accessory modules.</p>	10	700-ADL3	
	<p>Varistor with LED Surge Suppressor Voltage Range: 6...24V AC used with sockets that accept plug-in accessory modules.</p>	10	700-AV1R	
	<p>Varistor with LED Surge Suppressor Voltage Range: 110...240V AC used with sockets that accept plug-in accessory modules.</p>	10	700-AV3R	
	<p>RC Surge Suppressor Voltage Range: 6...24V AC/DC used with sockets that accept plug-in accessory modules.</p>	10	700-AR1	
	<p>RC Surge Suppressor Voltage Range: 110...240V AC/DC used with sockets that accept plug-in accessory modules.</p>	10	700-AR2	
	<p>Timing Module On-Delay or One-Shot selectable voltage range: 12...24V AC/DC used with sockets that accept plug-in accessory modules.</p>	<p>On-Delay</p> 	1	700-AT3
	<p>Timing Module On-Delay or One-Shot selectable voltage range: 110...125V AC used with sockets that accept plug-in accessory modules.</p>	<p>One-Shot</p> 		700-AT3A1
	<p>Timing Module On-Delay or One-Shot selectable voltage range: 230...240V AC used with sockets that accept plug-in accessory modules.</p>			700-AT3A2

§ Bulletin 700-HF Square Base Relay, Socket, and Retainer Clip Reference

Relay Type	Cat. No. Socket	Cat. No. Retainer Clip
700-HF32	700-HN116 700-HN262	700-HN114
700-HF34	700-HN139 700-HN264	700-HN266