

Two-Color Molded Legend Caps — Non-Illuminated Push Buttons

800F – AF    3    01  
                   *a*        *b*        *c*



Cat. No. 800F-15YSE112

*a*

Button Cap Type	
Code	Description
AF	Flush
AE	Extended

*b*

Color Cap	
Code	Description
1	White
2	Black
3	Green
4	Red
5	Yellow
6	Blue

*c*


Legend Text*†	
English	
Code	Description
01	START
02	STOP
05	O
06	I
08	→
09	FORWARD*
10	REVERSE*
11	R

\* Available in flush only.  
 \* White and yellow caps have black text. All other color caps have white text.  
 † Valid color cap text codes include:

Color	Text	
	Flush Caps	Extended Caps
White	FORWARD, REVERSE, START, I, →, R	→, R
Black	FORWARD, REVERSE, →, R	STOP, O, →, R
Green	FORWARD, REVERSE, START, I, →	→
Red	FORWARD, REVERSE, STOP, O, →	STOP, O, →
Yellow	FORWARD, REVERSE, →	→
Blue	FORWARD, REVERSE, →, R	→, R

Emergency Stop Legend Plates§

800F – 15YS              
                   *a*        *b*



*a*

Size/Color (Yellow)	
Code	Description
15Y	60 mm round (30.5 mm mounting hole)
15YS	60 mm round (22.5 mm mounting hole)➤
16Y	90 mm round (22.5 mm mounting hole)➤

*b*

Text	
Code	Description
Blank	No text
E112	EMERGENCY STOP
F112	ARRÊT D'URGENCE‡
S112	PARADA DE EMERGENCIA
G112	NOT HALT
T112	ARRESTO EMERGENZA
N112	NÖDSTOPP, EMERGENCY STOP‡

*b (cont'd)*

Text	
Code	Description
W112	NÖDSTOPP, EMERGENCY STOP‡
A112	NÖDSTOP
B112	EMERGENCY STOP, ARRÊT D'URGENCE, PARADA DE EMERGENCIA‡
D112	NOODSTOP‡
M112	NOT HALT, ARRESTO EMERGENZA, ARRÊT D'URGENCE➤
	EMERGENCY STOP, ARRÊT D'URGENCE, NOT HALT❖
L112	NEYDARSTOPP, NEYDARSTOPP‡
H112	NÖD-STOP, HÄTÄ-SEIS, NÖD-STOP‡

§ Sold only multiples of 10. Order (quantity of) 10 to receive one package of 10 pieces.  
 ➤ Not for use with base mounted contact blocks.  
 ‡ Not available on 15YS version.  
 ➤ Text printed on the 15Y version only.  
 ❖ Text printed on the 15YS & 16Y versions only.

10