




## Insulating Bushings

For Rigid • IMC. Press fit.  
Holds firmly in place while pulling cables.



Example:  
Telephone cable  
protected by Rigid  
insulating bushing.


Meets 2011 NEC code requirements for 300-15(c) protection. Listed for use in environmental air handling spaces per 2011 NEC code requirements 300-22(c).

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| RGD50          | 51930                    | 1/2        | 100      | 1000    | .531  | .989  |
| RGD75          | 51932                    | 3/4        | 100      | 1000    | .531  | 1.185 |
| RGD100         | 51933                    | 1          | 100      | 100     | .625  | 1.542 |
| RGD125         | 51934                    | 1-1/4      | 100      | 100     | .625  | 1.891 |
| RGD150         | 51935                    | 1-1/2      | 100      | 100     | .625  | 2.062 |
| RGD200         | 51936                    | 2          | 50       | 50      | .625  | 2.655 |
| EMT250†        | 12240                    | 2-1/2      | 25       | 25      | 1.225 | 3.062 |
| EMT300†        | 12245                    | 3          | 25       | 25      | 1.225 | 3.690 |
| EMT350†        | 12250                    | 3-1/2      | 25       | 25      | 1.231 | 4.187 |
| EMT400†        | 12255                    | 4          | 25       | 25      | 1.233 | 4.815 |



See page B-1 for EMT Insulating Bushings size 1/2" through 4".  
† Can also be used for EMT.



E105706 LR49636



Arlington's Rigid Insulating Bushings protect cables from abrasion by rigid. Examples: Power, Cable TV, computer datalines, telephone/modem, a/v cables, alarm systems, security systems. Rigid is often used to protect cables where damage could occur in a house or building.



Place board over bushing and tap onto Rigid or EMT with hammer.

## Zinc Combination Couplings EMT to Rigid

EMT compression to screw-in flexible metal conduit.  
Zinc die-cast.



2400

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | TRADE SIZE | UNIT PKG | STD PKG | DIM A | DIM B | DIM C |
|----------------|--------------------------|------------|----------|---------|-------|-------|-------|
| 2400           | 06920                    | 1/2"       | 50       | 50      | 1.000 | 1.267 | .946  |
| 2410           | 06921                    | 3/4"       | 50       | 50      | 1.000 | 1.412 | 1.200 |
| 2411           | 06922                    | 3/4"       | 50       | 50      | 1.210 | 1.475 | 1.200 |

Use with any listed fitting.

