

EMT Set-Screw Couplings

Concrete tight. Zinc die-cast.



810




816

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | Trade Size | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| 810* | 00810 | 1/2 | 50 | 500 | .950 | 1.560 |
| 811* | 00811 | 3/4 | 25 | 250 | 1.145 | 1.869 |
| 812* | 00812 | 1 | 15 | 150 | 1.435 | 2.000 |
| 813 | 00813 | 1-1/4 | 20 | 120 | 1.828 | 2.500 |
| 814 | 00814 | 1-1/2 | 10 | 60 | 2.075 | 2.890 |
| 815 | 00815 | 2 | 5 | 30 | 2.535 | 2.567 |
| 816† | 00816 | 2-1/2 | 12 | 12 | 3.280 | 4.000 |
| 817† | 00817 | 3 | 12 | 12 | 3.910 | 4.500 |
| 8175† | 08175 | 3-1/2 | 6 | 6 | 4.460 | 4.814 |
| 818† | 00818 | 4 | 6 | 6 | 4.984 | 5.269 |

*Add suffix "RH" for Robertson Head Screws.

†Listed for use with steel and aluminum EMT, IMC, and rigid conduit.



EMT Compression Couplings

UL listed concrete tight. CSA listed concrete tight/rain tight. Zinc die-cast.



830



836

| CATALOG NUMBER | UPC/DCI/NAED MFG #018997 | Trade Size | UNIT PKG | STD PKG | DIM A | DIM B |
|----------------|--------------------------|------------|----------|---------|-------|-------|
| 830 | 00830 | 1/2 | 50 | 500 | 1.550 | 1.080 |
| 831 | 00831 | 3/4 | 25 | 250 | 1.615 | 1.313 |
| 832 | 00832 | 1 | 15 | 150 | 1.692 | 1.616 |
| 833 | 00833 | 1-1/4 | 10 | 100 | 2.160 | 2.080 |
| 834 | 00834 | 1-1/2 | 10 | 60 | 2.290 | 2.380 |
| 835 | 00835 | 2 | 10 | 60 | 2.600 | 2.910 |
| 836 | 00836 | 2-1/2 | 12 | 12 | 3.070 | 3.470 |
| 837 | 00837 | 3 | 12 | 12 | 3.300 | 4.133 |
| 838 | 00838 | 3-1/2 | 6 | 6 | 3.330 | 4.775 |
| 839 | 00839 | 4 | 6 | 6 | 3.445 | 5.300 |

