

IN BOX™ for New Brick

LOOK!
more on
reverse

Non-metallic • Low Profile Box with Adapter Sleeve



White

DHB1C
Cover removed
to show installation



Brown

DHB1BRC
Finished installation

Meets NEC 2008

Section 406-8; for the protection of exterior outlets which require the use of a weatherproof-while-in-use cover for all outdoor 15 or 20 AMP receptacles.



**Installs in
the wall –
Less
shows
outside!**

Arlington's **IN-BOX™** – the recessed weatherproof-in-use electrical box for new brick offers features that get the job done fast – and right!

Our new brick IN BOX in both horizontal or vertical orientation, comes with a protective adapter sleeve which keeps mortar out of the box while the brick mason completes his installation.

When you're ready to finish the electrical installation, just slip the clean IN-BOX into the sleeve...easy!


- One-piece design replaces the installation of an electrical box and bubble cover assembly
- Clean, great-looking weatherproof installation
- Built-in anchor tabs seat adapter sleeve into mortar for a super secure installation
- Kit includes IN-BOX electrical box in brown to match the brick, or white with a clear cover, and an NM cable connector – also an adapter sleeve, caulk, one standard duplex, and one GFCI wall plate.

A  
Arlington

1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

IN BOX™ for New Brick

Non-metallic • Low Profile Box with Adapter Sleeve



DHB1BRC

Brown box w/ clear cover



1 Mortar in adapter sleeve. Pull wire and tie off to loop in adapter sleeve.



2 When ready to complete...apply supplied caulk as shown and press around edges of adapter sleeve.



3 Install the supplied NM cable connector and wire. Insert the clean IN BOX into the adapter sleeve.



4 Attach IN BOX with the screws provided. Install wiring device per manufacturer's instructions.



5 Install wiring device. IN BOX accepts most single gang wiring devices and uses a standard indoor wall plate. Plug in a cord for a weatherproof-while-in-use finished installation.



Arlington
1 Stauffer Industrial Park
Scranton, PA 18517

800/233.4717

Fax 570/562.0646

www.aifittings.com

© 2006 Arlington Industries, Inc. REV Web 06/10

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	ORIENTATION & COLOR	UNIT PKG	STD PKG
DHB1C	54880	Horiz/Clear cover/White box	1	4
DHB1W	54882	Horiz/White cover/White box	1	4
DHB1BRC	54881	Horiz/Clear cover/Brown box	1	4
DHB1BR	54875	Horiz/Brown cover/Brown box	1	4
DVB1C	43609	Vertical/Clear cover/White box	1	4
DVB1W	43620	Vertical/White cover/White box	1	4
DVB1BRC	43608	Vertical/Clear cover/Brown box	1	4
DVB1BR	43595	Vertical/Brown cover/Brown box	1	4

IN BOX for new brick includes box w/ weatherproof-in-use cover, adapter sleeve, installed bug plugs, (1) standard duplex and (1) GFCI face plate, installation screws, (1) NM cable connector, (1) roll of caulk and a disposable mud cover.

Add suffix 'CG' to Catalog # when ordering for use in Canada, i.e. DHB1CGC.

Distributed by