

HID Flood Lights

250 – 1000W PS | HPS

FEATURES

- Die Cast Aluminum Housing
- Hinged Face Frame
- Tempered Glass Lens
- High Output Reflector
- UL Listed for Ground Mounting
- Pre-wired with Cord

FLL Series

16" Die Cast Flood Light



ORDERING INFORMATION

CATALOG #	DESCRIPTION	VOLTS	BALLAST TYPE	LAMP
Pulse Start				
FLL-250PQPK	250 watt PS	Quad	CWA	MS250/H
FLL-400PQPK	400 watt PS	Quad	CWA	MS400/H
FLL-400P5PK	400 watt PS	5-Tap	CWA	MS400/H
High Pressure Sodium				
FLL-400H5PK	400 watt HPS	5-Tap	CWA	C400S51

For Slipfitter Add Suffix "S"

FEATURES

- Die Cast Aluminum Housing
- Hinged Face Frame
- Tempered Glass Lens
- High Output Reflector
- UL Listed for Ground Mounting
- Pre-wired with Cord

FLLX Series

23" Die Cast Flood Light



ORDERING INFORMATION

CATALOG #	DESCRIPTION	VOLTS	BALLAST TYPE	LAMP
Metal Halide				
FLLX-1000MHQPKT	1000 watt MH w/ Trunion	Quad	CWA	MH1000/U
FLLX-1000MHQPKS	1000 watt MH w/ Slipfitter	Quad	CWA	MH1000/U
FLLX-1000MH5PKT	1000 watt MH w/ Trunion	5-Tap	CWA	MH1000/U
FLLX-1000MH5PKS	1000 watt MH w/ Slipfitter	5-Tap	CWA	MH1000/U
High Pressure Sodium				
FLLX-1000HQPKT	1000 watt HPS w/ Trunion	Quad	CWA	C1000S52
FLLX-1000HQPKS	1000 watt HPS w/ Slipfitter	Quad	CWA	C1000S52

Accessories

Mounting

ORDERING INFORMATION

CATALOG #	DESCRIPTION	FINISH
FP19BL	17 1/2" Pedestal w/ 1 Piece Molded Cap; 1/2" Threaded NPS for Fixture Mounting	Black
280-032	Adjustable Post Top Fitter 1/2" Threaded Apertures	Bronze
320-035BZ	Slipfitter for FLDX	Bronze
280-016-1	Slipfitter for FLL	Bronze

Face Frame Assemblies

ORDERING INFORMATION

CATALOG #	DESCRIPTION	FINISH
210-001	FL Face Frame Assembly	Bronze
210-004	FLM Face Frame Assembly	Bronze
210-002	FLDX Face Frame Assembly	Bronze

