





NEMA 12 SINGLE DOOR ENCLOSURES

Type 4 & 12
Enclosures



**INDUSTRY
STANDARDS**

UL 50 Type 12
UL 508 Type 12
NEMA Type 12
CUL Type 12

Austin Electrical Enclosures
Post Office Box 2320
Yadkinville, NC 27055

Phone: 336.468.2851
800.288.2851

NEMA 12 SINGLE DOOR ENCLOSURES

Austin NEMA 12 single door enclosures are Underwriters Laboratories Listed and are designed for indoor use primarily to provide a degree of protection against circulating dust, falling dirt, and dripping noncorrosive liquids.

Construction:

- Fabricated in accordance with UL specifications from code gauge steel.
- Continuously welded seams ground smooth.
- Door removed by pulling continuous hinge pin.
- Neoprene gasket attached to door with oil resistant adhesive.
- Hasp and staple provided for padlocking.
- External feet for mounting enclosure.
- Standard plastic self-adhesive print pocket.
- Standard collar studs for mounting optional panel.

Finish:

Austin Type 12 Single door enclosures are provided standard with an ANSI 61 gray polyester powder coating inside and out. Optional panels are finished white.


Options:

- Special materials.
- Special finishes.
- Custom box size or construction.



NEMA 12 SINGLE DOOR ENCLOSURES

Type 4 & 12
Enclosures



**INDUSTRY
STANDARDS**

UL 50 Type 12
UL 508 Type 12
NEMA Type 12
CUL Type 12

Austin Electrical Enclosures
Post Office Box 2320
Yadkinville, NC 27055

Phone: 336.468.2851
800.288.2851

NEMA 12 SINGLE DOOR ENCLOSURES

Catalog Number	Enclosure Size (AxBxC)	Enclosure Weight	Panel Catalog Number	Panel Weight	Catalog Number	Enclosure Size (AxBxC)	Enclosure Weight	Panel Catalog Number	Panel Weight
AB-12246N	12x24x6	29	AB-1224TP	8	AB-202010N	20x20x10	44	AB-2020TP	9
AB-16126N	16x12x6	22	AB-1612TP	4	AB-241210N	24x12x10	36	AB-2412TP	7
AB-16166N	16x16x6	27	AB-1616TP	6	AB-242010N	24x20x10	50	AB-2420TP	13
AB-20126N	20x12x6	26	AB-2012TP	5	AB-242410N	24x24x10	56	AB-2424TP	15
AB-20166N	20x16x6	31	AB-2016TP	7	AB-302010N	30x20x10	60	AB-3020TP	16
AB-16206N	16x20x6	31	AB-1620TP	7	AB-302410N	30x24x10	68	AB-3024TP	19
AB-20206N	20x20x6	36	AB-2020TP	9	AB-362410N	36x24x10	78	AB-3624TP	24
AB-24126N	24x12x6	30	AB-2412TP	7	AB-363010N	36x30x10	96	AB-3630TP	30
AB-24166N	24x16x6	37	AB-2416TP	9	AB-423010N	42x30x10	108	AB-4230TP	35
AB-20246N	20x24x6	42	AB-2024TP	13	AB-423610N	42x36x10	126	AB-4236TP	43
AB-24206N	24x20x6	41	AB-2420TP	13	AB-483010N	48x30x10	120	AB-4830TP	40
AB-24246N	24x24x6	48	AB-2424TP	15	AB-483610N	48x36x10	141	AB-4836TP	49
AB-30166N	30x16x6	41	AB-3016TP	12	AB-603610N	60x36x10	169	AB-6036TP	61
AB-30206N	30x20x6	51	AB-3020TP	16					
AB-30246N	30x24x6	58	AB-3024TP	19	AB-201612N	20x16x12	41	AB-2016TP	7
AB-36246N	36x24x6	69	AB-3624TP	24	AB-242012N	24x20x12	54	AB-2420TP	13
AB-36306N	36x30x6	84	AB-3630TP	30	AB-242412N	24x24x12	61	AB-2424TP	15
					AB-302412N	30x24x12	73	AB-3024TP	19
AB-16128N	16x12x8	24	AB-1612TP	4	AB-303012N	30x30x12	89	AB-3030TP	24
AB-16168N	16x16x8	31	AB-1616TP	6	AB-362412N	36x24x12	83	AB-3624TP	24
AB-20128N	20x12x8	28	AB-2012TP	5	AB-363012N	36x30x12	102	AB-3630TP	30
AB-20168N	20x16x8	34	AB-2016TP	7	AB-363612N	36x36x12	117	AB-3636TP	37
AB-16208N	16x20x8	34	AB-1620TP	7	AB-423012N	42x30x12	115	AB-4230TP	35
AB-20208N	20x20x8	40	AB-2020TP	9	AB-423612N	42x36x12	132	AB-4236TP	43
AB-24128N	24x12x8	33	AB-2412TP	7	AB-483612N	48x36x12	148	AB-4836TP	49
AB-12248N	12x24x8	33	AB-1224TP	7	AB-603612N	60x36x12	178	AB-6036TP	61
AB-24168N	24x16x8	40	AB-2416TP	15	AB-723012N	72x30x12	177	AB-7230TP	62
AB-24208N	24x20x8	46	AB-2420TP	13					
AB-20248N	20x24x8	46	AB-2024TP	13					
AB-24248N	24x24x8	52	AB-2424TP	15	AB-242016N	24x20x16	62	AB-2420TP	13
AB-30208N	30x20x8	55	AB-3020TP	16	AB-242416N	24x24x16	70	AB-2424TP	15
AB-30248N	30x24x8	63	AB-3024TP	19	AB-302416N	30x24x16	82	AB-3024TP	19
AB-24308N	24x30x8	62	AB-2430TP	19	AB-363016N	36x30x16	114	AB-3630TP	30
AB-30308N	30x30x8	75	AB-3030TP	30	AB-423616N	42x36x16	147	AB-4236TP	43
AB-36248N	36x24x8	72	AB-3624TP	24	AB-483616N	48x36x16	164	AB-4836TP	49
AB-36308N	36x30x8	90	AB-3630TP	30	AB-603616N	60x36x16	195	AB-6036TP	61
AB-30368N	30x36x8	89	AB-3036TP	30	AB-723016N	72x30x16	196	AB-7230TP	62
AB-36368N	36x36x8	102	AB-3636TP	37					
AB-42248N	42x24x8	82	AB-4224TP	28	AB-722418N	72x24x18	157	AB-7224TP	49
AB-42308N	42x30x8	101	AB-4230TP	35					
AB-42368N	42x36x8	119	AB-4236TP	43	AB-302420N	30x24x20	92	AB-3024TP	19
AB-48248N	48x24x8	92	AB-4824TP	32	AB-363020N	36x30x20	125	AB-3630TP	30
AB-48308N	48x30x8	113	AB-4830TP	40	AB-483620N	48x36x20	178	AB-4836TP	49
AB-48368N	48x36x8	133	AB-4836TP	49	AB-603620N	60x36x20	211	AB-6036TP	61
AB-60368N	60x36x8	160	AB-6036TP	61	AB-723020N	72x30x20	215	AB-7230TP	62
AB-161210N	16x12x10	27	AB-1612TP	4	AB-722424N	72x24x24	184	AB-7224TP	49
AB-201610N	20x16x10	38	AB-2016TP	7	AB-723024N	72x30x24	234	AB-7230TP	62