

FS59US (Nickel) RG59US (Gold)	RG59 F-type, Universal Splice (Red)	LMTIP-WP	CPLCCT-SLM
FS59RCAUS (Nickel) RG59RCAUS (Gold)	RG59 RCA, Universal Splice (Red)	LMTIP-WP	CPLCCT-SLM
FS59BNCUS (Nickel) RG59BNCUS (Gold)	RG59 BNC, Universal Splice (Red)	NONE	CPLCCT-SLM
FS6US (Nickel) RG6US (Gold)	RG6 F-type, Universal Splice (Green)	LMTIP-WP	CPLCCT-SLM
FS6RCAUS (Nickel) RG6RCAUS (Gold)	RG6 RCA, Universal Splice Connector (Green)	LMTIP-WP	CPLCCT-SLM
FS6BNCUS (Nickel) RG6BNCUS (Gold)	RG6 BNC, Universal Splice Connector (Green)	NONE	CPLCCT-SLM

## Double Bubble™ Compression Connectors

INDUSTRY USE: SECURITY • BROADCAST • COMMERCIAL  
LAW ENFORCEMENT • CATV • SATELLITE

- Double Bubble™ compression connectors are designed for structured wiring, security cameras and other exposed wiring installations
- F, RCA and BNC for RG59 and RG6 cables
- BNC and RCA connectors for RGB/ mini coax cables



### Double Bubble Compression Connectors

Part#	Connector Description	Tip Req'd	Tool Req'd
DB1RCA	RGB/ Mini Coax (25-26AWG) RCA (Orange)	LMTIP-S	CPLCRBC-B
DB1BNC	RGB/ Mini Coax (25-26AWG) BNC (Orange)	NONE	CPLCRBC-B
DB15RCA	RGB/ Mini Coax (22-24AWG) RCA (Purple)	LMTIP-S	CPLCRBC-B
DB59U	RG59 F-type Double Bubble™ connector	LMTIP-S	CPLCRBC-B
DB59RCAU	RG59 RCA Double Bubble™ connector	LMTIP-S	CPLCRBC-B
DB59BNCU	RG59 BNC Double Bubble™ connector	NONE	CPLCRBC-B
DB6U	RG6 F-type Double Bubble™ connector	LMTIP-S	CPLCRBC-B
DB6RCAU	RG6 RCA Double Bubble™ connector	LMTIP-S	CPLCRBC-B

**NOTE:** All cable for Belden compression connectors should be sized using the Belden Cable Sizing Chart located on pages 40-43 or at [www.icmcorp.net/ICM\\_techinfo.com](http://www.icmcorp.net/ICM_techinfo.com)