

Labelizer® Plus and VersaPrinter™ Supplies

BradyID.com/s34



Discontinued Printer Supplies Still Available!

Material tapes for the Labelizer® PLUS and VersaPrinter™ machines are still manufactured and fully stocked. View all available parts on the following pages.

Labelizer® Plus Industrial Labeling System



VersaPrinter™ Label & Sign Maker



Indoor/Outdoor Vinyl Tape (B-595)

- Adheres to pipes, walls, equipment, windows – most clean, dry surfaces
- Conforms well to irregular, curved or rough surfaces
- Ideal for general purpose industrial uses – stands up to grease, oil and most industrial chemicals
- 8-10 year average outdoor durability in temperatures from 180°F to -40°F (82°C to -40°C) and can be applied as low as 0°F (-18°C)



Catalog #	B#	Color	Label Width A Inch (mm)	Roll Length B Feet (m)	Cartridges Per Pkg.
142760	B-595	Black on Clear	0.500 (12.7)	90 ft (27.4 m)	2
142759	B-595	Black on Clear	1.125 (28.6)	90 ft (27.4 m)	2
142758	B-595	Black on Clear	2.250 (57.2)	90 ft (27.4 m)	1
142757	B-595	Black on Clear	4.000 (101.6)	90 ft (27.4 m)	1
142762	B-595	White on Clear	2.250 (57.2)	90 ft (27.4 m)	1
142765	B-595	Black on Green	1.125 (28.6)	90 ft (27.4 m)	2
142764	B-595	Black on Green	2.250 (57.2)	90 ft (27.4 m)	1
142763	B-595	Black on Green	4.000 (101.6)	90 ft (27.4 m)	1
142750	B-595	Black on Yellow	0.500 (12.7)	90 ft (27.4 m)	2
142749	B-595	Black on Yellow	1.125 (28.6)	90 ft (27.4 m)	2
142748	B-595	Black on Yellow	2.250 (57.2)	90 ft (27.4 m)	1
142747	B-595	Black on Yellow	3.000 (76.2)	90 ft (27.4 m)	1
142746	B-595	Black on Yellow	4.000 (101.6)	90 ft (27.4 m)	1
142769	B-595	White on Green	0.500 (12.7)	90 ft (27.4 m)	2
142768	B-595	White on Green	1.125 (28.6)	90 ft (27.4 m)	2
142767	B-595	White on Green	2.250 (57.2)	90 ft (27.4 m)	1
142766	B-595	White on Green	4.000 (101.6)	90 ft (27.4 m)	1
142777	B-595	White on Blue	0.500 (12.7)	90 ft (27.4 m)	2
142776	B-595	White on Blue	1.125 (28.6)	90 ft (27.4 m)	2
142775	B-595	White on Blue	2.250 (57.2)	90 ft (27.4 m)	1
142774	B-595	White on Blue	4.000 (101.6)	90 ft (27.4 m)	1
142745	B-595	Red on White	0.500 (12.7)	90 ft (27.4 m)	2
142744	B-595	Red on White	1.125 (28.6)	90 ft (27.4 m)	2
142743	B-595	Red on White	2.250 (57.2)	90 ft (27.4 m)	1
142742	B-595	Red on White	4.000 (101.6)	90 ft (27.4 m)	1
142772	B-595	White on Red	0.500 (12.7)	90 ft (27.4 m)	2
142773	B-595	White on Red	1.125 (28.6)	90 ft (27.4 m)	2
142771	B-595	White on Red	2.250 (57.2)	90 ft (27.4 m)	1
142770	B-595	White on Red	4.000 (101.6)	90 ft (27.4 m)	1
142741	B-595	Black on White	0.500 (12.7)	90 ft (27.4 m)	2
142740	B-595	Black on White	1.125 (28.6)	90 ft (27.4 m)	2
142739	B-595	Black on White	2.250 (57.2)	90 ft (27.4 m)	1
142738	B-595	Black on White	3.000 (76.2)	90 ft (27.4 m)	1
142737	B-595	Black on White	4.000 (101.6)	90 ft (27.4 m)	1
142756	B-595	Black on Orange	0.500 (12.7)	90 ft (27.4 m)	2
142755	B-595	Black on Orange	1.125 (28.6)	90 ft (27.4 m)	2
142754	B-595	Black on Orange	2.250 (57.2)	90 ft (27.4 m)	1
142753	B-595	Black on Orange	4.000 (101.6)	90 ft (27.4 m)	1
142785	B-595	Black on Gray	0.500 (12.7)	90 ft (27.4 m)	2
142784	B-595	Black on Gray	1.125 (28.6)	90 ft (27.4 m)	2
142783	B-595	Black on Gray	2.250 (57.2)	90 ft (27.4 m)	1
142782	B-595	Black on Gray	4.000 (101.6)	90 ft (27.4 m)	1

Continued on next page.

