



## Lockout/Tagout

Keep your most valuable resource safe from hazardous energy at your mining site by implementing a lockout/tagout program for your employees. With both fatal and non-fatal electrical accidents being reported as a main MSHA violation, it's important to make sure circuits are locked, grounded, and tagged prior to any maintenance work being performed.



### Regulations

The following MSHA regulations protect your employees:

- **§ 56.12016 & § 57.12016** Work on electrically powered equipment
- **§ 57.509 & § 77.500** Danger signs at electrical installations



## All Purpose Cable Lockout

- Compact, lightweight body made of rugged Isoplast can be used in a variety of applications
- Available with two types of cables: nonconductive nylon and sheathed metal

Catalog #	Description
50943	Lockout w/ 8' sheathed metal cable
50941	Lockout w/ 8' non-conductive nylon cable
50944	Lockout without cable



## Gate Valve Lockouts

- Made of rugged injection-molded polypropylene
- Available in 5 sizes, and additional colors including yellow, green, and blue

Fits Valve Handles Dia.	Red
1" to 2-1/2"	65560
2-1/2" to 5"	65561
5" to 6-1/2"	65562
6-1/2" to 10"	65563
10" to 13"	65564



## Prinzing Ball Valve Lockout

- Small lockout locks out pipes 1/2" to 2 1/2" in diameter, Large lockout locks out pipes 2" to 8" in diameter
- Also available in yellow, green, and blue"

Size	Red
Small	BS07A
Large	BS08A



## Compact & Safety Padlocks

- Superior temperature, chemical and corrosion resistance
- Body is nonconductive and comes with key retaining feature
- Ideal for your lockout/tagout program

Color	Keyed Different 1/Pack	Keyed Different 6/Pack	Keyed Alike 3/Pack	Keyed Alike 6/Pack
<b>Compact Safety Padlocks</b>				
Red	143150	118926	118953	118954
Green	143152	118927	118955	118956
Blue	143156	118929	118959	118960
Yellow	143158	118930	118961	118962
<b>Safety Padlocks</b>				
Red	99552	51339	105886	105890
Green	99564	51345	105889	105893
Blue	99556	51344	105887	105891
Yellow	99570	51346	105888	105892

\*Brady offers additional colors as well as steel padlocks, and aluminum padlocks - including custom options. When keyed alike, all locks in a set can be opened with the same key. This option is beneficial when multiple locks are assigned to a single employee.



## Steel Group Lockout Hasps

- Constructed of vinyl-coated high tensile steel w/ rust resistant plating
- Lock holes: 3/8" diameter

Catalog #	Description	Qty.
65375	1" Diameter Jaws	12
65376	1-1/2" Diameter Jaws	12



## Portable Metal Group Lockout Boxes

- Made of heavy duty steel, powder-coated for extra rust resistance
- Essential for group lockout situations

Catalog #	Description	Size
65699	Red - Standard	6"H x 9"W x 3-1/2"D
51171	Red - XL	6"H x 7-3/8"W x 9-1/2"D

\* Padlocks sold separately.

## Standard Lockout Tags

- Communicate safety and lockout information at the point of need with the wide selection of Lockout/Tagout tags.

Catalog #	Reverse Legend	Qty.
<b>Heavy Duty Polyester 5-1/2" x 3"</b>		
65502	Side B	25
65670	Side G	25
<b>Economy Polyester 5-3/4" x 3"</b>		
66050	Side B	25
66052	Side G	25
<b>Cardstock 5-3/4" x 3"</b>		
65407	Side B	25
65440	Side G	25



## Electrical Lockout

- Extremely versatile - work on a wide range of breaker sizes and types!
- View Brady's Circuit Breaker Lockout Reference Guide to find out which device is right for your breaker



Catalog #	Description	Qty.
65396	120/277V Clamp-On Breaker Lockout	1
65397	480/600V Clamp-On Breaker Lockout	1
66321	Universal Multi-Pole Breaker Lockout	1
65329	Oversized Breaker Lockout	1