

## Indoor/Outdoor Vinyl Tape

- **B-595 Vinyl Tape** - Super-tough and perfect for voice, data, audio, video, HVAC control, bins, safety and electrical applications.



Color		0.375" x 21' (9.530 mm x 6.400 m)	0.500" x 21' (12.700 mm x 6.400 m)	0.750" x 21' (19.050 mm x 6.400 m)
Black on White		M21-375-595-WT	M21-500-595-WT	M21-750-595-WT
Black on Yellow		M21-375-595-YL	M21-500-595-YL	M21-750-595-YL
White on Red		M21-375-595-RD	M21-500-595-RD	M21-750-595-RD
White on Blue		M21-375-595-BL	M21-500-595-BL	M21-750-595-BL
White on Green		M21-375-595-GN	M21-500-595-GN	M21-750-595-GN
Black on Orange		M21-375-595-OR	M21-500-595-OR	M21-750-595-OR

Note: As of March 2011, B-580 material has been replaced by B-595 material. The updated part numbers are shown in table above. For example: part number "M21-375-580-WT" has been replaced with "M21-375-595-WT".



## Self-Laminating Wire Markers

### B-427 Self-Laminating Vinyl Labels

- Excellent water, oil and abrasion resistance.

Part Number	Material	Color	Label Width
M21-750-427*	B-427	Black on White	0.75" x 14' (19.05 mm x 4.27 m)
M21-1000-427*	B-427	Black on White	1.00" x 14' (25.40 mm x 4.27 m)
M21-1250-427*	B-427	Black on White	1.25" x 14' (31.75 mm x 4.27 m)
M21-1500-427*	B-427	Black on White	1.50" x 14' (38.10 mm x 4.27 m)

\*not compatible in the ID PAL™ Printer.



## PermaSleeve® Wire Marker Sleeves

### B-342 PermaSleeve® PS Polyolefin Wire Marking Sleeves

- Continuous Cut-to-Length Heat Shrinkable Sleeves.

Part Number	Material	Color	Size
M21-125-C-342*	B-342	Black on White	0.235" x 7' (5.970 mm x 2.13 m)
M21-187-C-342	B-342	Black on White	0.335" x 7' (8.510 mm x 2.13 m)
M21-250-C-342	B-342	Black on White	0.439" x 7' (11.150 mm x 2.13 m)
M21-375-C-342	B-342	Black on White	0.645" x 7' (16.380 mm x 2.13 m)


\*not compatible in the ID PAL™ Printer.



## Nylon Cloth

**B-499 Nylon Cloth Labels** - Permanent adhesive for wire, cable, patch panels, faceplates and terminal blocks.

Part Number	Material	Color	Description
<b>For wire, cable, patch panels and faceplates.</b>			
M21-375-499	B-499	Black on White	0.375" x 16' (9.530 mm x 4.88 m)
M21-500-499	B-499	Black on White	0.500" x 16' (12.70 mm x 4.88 m)
M21-750-499	B-499	Black on White	0.750" x 16' (19.05 mm x 4.88 m)
<b>For terminal blocks</b>			
M21-375-499-TB	B-499	Black on White	0.375" x 16' (9.530 mm x 4.88 m)
M21-500-499-TB	B-499	Black on White	0.500" x 16' (12.70 mm x 4.88 m)



## Polyester

### • B-423 Polyester Labels and B-430 Polyester Labels

- For instruments, racks and bins

Part Number	Material	Color	Description
M21-375-423	B-423	Black on White	0.375" x 21' (9.530 mm x 6.400 m)
M21-500-423	B-423	Black on White	0.500" x 21' (12.700 mm x 6.400 m)
M21-750-423	B-423	Black on White	0.750" x 21' (19.050 mm x 6.400 m)
M21-375-430	B-430	Black on Clear	0.375" x 21' (9.530 mm x 6.400 m)
M21-500-430	B-430	Black on Clear	0.500" x 21' (12.700 mm x 6.400 m)
M21-750-430	B-430	Black on Clear	0.750" x 21' (19.050 mm x 6.400 m)



### BMP®21 Label Printer - Did You Know?



1. The necessary print ribbons for the BMP®21 Label Printer are self-contained within the label roll cartridge. So there's no need to order or load separate print ribbons!
2. BMP®21 consumables are also compatible with the ID Pal™ Label Printer unless otherwise noted..

