



TLS 2200®/TLS PC Link™ Labels - # PTL-31-423

SIZE: 1.500" W x 1.000" H (38.100 mm W x 25.400 mm H)
MATERIAL: Permanent Polyester
QTY/UOM: 250/Roll
CATALOG #: PTL-31-423
PRODUCT #: 18427
\$34.78 MSRP (\$US)

OVERVIEW SPECIFICATIONS

Description for TLS 2200®/TLS PC Link™ Labels

BradyBondz™ Labels for the TLS 2200® & TLS-PC Link™ Thermal Transfer Portable Printers. Please Note: This material is UL, CSA & AGA approved with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.

Specification Of TLS 2200®/TLS PC Link™ Labels

Application(s): Asset Tracking, Barcoding, Bottles, Component ID, Conical Tube, Deep Well Plate, Equipment ID, General Identification, General Purpose ID, Petri Dish, Rating Plates, Through Hole - Top

Agency Approval(s)/Compliance: AGA Approved, CSA Approved, Halogen-Free (DIN VDE 0472/parts 815), UL Recognized

Size: 1.500" W x 1.000" H (38.100 mm W x 25.400 mm H)

Printable Area: 1.500" W x 1.000" H (38.100 mm W x 25.400 mm H)

Max Characters Per Line For Font #2: 37

Max Lines of Text For Font #2: 10

Label Type/Style: Label

Color: White

Finish: Gloss

Qty Per Row: 1

Material Type: Polyester

Material Description: Permanent Polyester

Brady Material #: B-423

Safety Catalog: [pg. 234](#)

General ID Catalog: [pg. 25](#)

Recommended Ribbon Series: R6010

Suggested Ribbon Part#: R6010

Acceptable Ribbon Series: R6210, R4410 (colors)

After Process: Yes, this material will work with this application

Environment: Autoclave

Printer Compatibility: BMP71, TLS 2200, TLS-PC Link

Surface: Smooth

Through Hole Technology: No, this material does not work with this application

Brand: WorkHorse Series

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 250/Roll