

## ASSET TRACKING MATERIALS

### B-435 Polyester Labels

**Color: Silver Metallic**      **Finish: Gloss**

Printable metallized polyester with glossy finish. Withstands numerous solvents and variable temps. Ideal for serial and rating plate applications with name-plate quality and a metal looking finish.




Figure 29




Figure 54



Diagram	Part Number	B-#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 29	PTL-16-435	B-435	Polyester	Silver	1.000 (25.4)	0.375 (9.5)	1	500	R6010
Fig. 29	PTL-17-435	B-435	Polyester	Silver	1.000 (25.4)	0.500 (12.7)	1	500	R6010
Fig. 29	PTL-19-435	B-435	Polyester	Silver	1.000 (25.4)	1.000 (25.4)	1	250	R6010
Fig. 29	PTL-29-435	B-435	Polyester	Silver	1.500 (38.1)	0.500 (12.7)	1	500	R6010
Fig. 29	PTL-30-435	B-435	Polyester	Silver	1.500 (38.1)	0.750 (19.1)	1	250	R6010
Fig. 29	PTL-31-435	B-435	Polyester	Silver	1.500 (38.1)	1.000 (25.4)	1	250	R6010
Fig. 29	PTL-32-435	B-435	Polyester	Silver	1.500 (38.1)	1.500 (38.1)	1	250	R6010
Fig. 54	PTL-35-435-PROP	B-435	Polyester	Black on Silver	1.630 (41.4)	0.750 (19.1)	1	250	R6010
Fig. 29	PTL-20-435	B-435	Polyester	Silver	2.000 (50.8)	1.000 (25.4)	1	100	R6010
Fig. 29	PTL-37-435	B-435	Polyester	Silver	3.000 (76.2)	1.900 (48.3)	1	100	R6010
Fig. 29	PTL-38-435	B-435	Polyester	Silver	4.000 (101.6)	1.900 (48.3)	1	100	R6010

### B-486 Polyester Labels

**Color: Silver Metallic**      **Finish: Matte**

Metallized polyester material designed for high adhesion to textured metals, powder coated surfaces and low surface energy plastics. Withstands numerous solvents and variable temps.




Figure 29




Figure 46  
(Includes black border)



Diagram	Part Number	B-#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 29	PTL-16-486	B-486	Polyester	Silver	1.000 (25.4)	0.375 (9.5)	1	500	R4310
Fig. 29	PTL-17-486	B-486	Polyester	White	1.000 (25.4)	0.500 (12.7)	1	500	R4310
Fig. 29	PTL-19-486	B-486	Polyester	Silver	1.000 (25.4)	1.000 (25.4)	1	250	R4310
Fig. 46	PTL-24-486-BK	B-486	Polyester	Silver/Black Border	1.130 (28.7)	0.500 (12.7)	1	500	R4310
Fig. 29	PTL-29-486	B-486	Polyester	Silver	1.500 (38.1)	0.500 (12.7)	1	500	R4310
Fig. 29	PTL-30-486	B-486	Polyester	Silver	1.500 (38.1)	0.750 (19.1)	1	250	R4310
Fig. 29	PTL-31-486	B-486	Polyester	Silver	1.500 (38.1)	1.000 (25.4)	1	250	R4310
Fig. 29	PTL-32-486	B-486	Polyester	Silver	1.500 (38.1)	1.500 (38.1)	1	250	R4310
Fig. 29	PTL-20-486	B-486	Polyester	Silver	2.000 (50.8)	1.000 (25.4)	1	100	R4310
Fig. 29	PTL-37-486	B-486	Polyester	Silver	3.000 (76.2)	1.900 (48.3)	1	100	R4310
Fig. 29	PTL-38-483	B-486	Polyester	White	4.000 (101.6)	1.900 (48.3)	1	100	R6010
Fig. 29	PTL-38-486	B-486	Polyester	Silver	4.000 (101.6)	1.900 (48.3)	1	100	R4310

## WIRE & CABLE MATERIALS

### B-109 Polyethylene Tags

**Color: White**      **Finish: Matte**

Excellent multi-purpose tag for identifying multiconductor cables, inventory, safety warning repair and work-in-processing manufacturing. Good weatherability, humidity resistance and legibility after solvent exposure.




Figure 45




Figure 50




Figure 56



Diagram	Part Number	B-#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 45	PTL-36-109	B-109	Polyethylene	White	1.125 (28.6)	1.750 (44.5)	1	250	R4310
Fig. 56	PTL-12-109	B-109	Polyethylene	White	3.000 (76.2)	0.750 (19.1)	1	100	R4310
Fig. 56	BPTL-12-109	B-109	Polyethylene	White	3.000 (76.2)	0.750 (19.1)	1	1000	R4310

See all TLS2200® and PC Link™ Ribbon parts on page 247.