



Stripes™ Outdoor Extension Cords



Increase safety awareness and help to prevent jobsite loss or theft with neon STRIPES™ outdoor extension cords. Each extension cord features a dominant color and an extruded colored stripe that runs the length of the cord. All STRIPES™ extension cords have a power indicator light in the receptacle to show that the power is on.



02549-88-3V

| CAT NO | WIRE GA/COND | WIRE TYPE | NEON COLOR | LENGTH IN FT | PACKAGE TYPE | 125V RATING | MASTER PACK | MASTER WT | MASTER PACK CUBE |
|-------------|--------------|-----------|-------------------|--------------|--------------|-------------|-------------|-----------|------------------|
| 02548-88-54 | 12/3 | SJTW | Lime Green/Red | 50 | Sleeve | 15A | 8 | 53 | 1.41 |
| 02548-88-22 | 12/3 | SJTW | Yellow Purple | 50 | Sleeve | 15A | 8 | 53 | 1.41 |
| 02548-88-52 | 12/3 | SJTW | Dark Green/Yellow | 50 | Sleeve | 15A | 8 | 53 | 1.41 |
| 02548-88-62 | 12/3 | SJTW | Blue/Yellow | 50 | Sleeve | 15A | 8 | 53 | 1.41 |
| 02548-88-64 | 12/3 | SJTW | Blue/Red | 50 | Sleeve | 15A | 8 | 53 | 1.41 |
| 02548-88-41 | 12/3 | SJTW | Red/White | 50 | Sleeve | 15A | 8 | 53 | 1.41 |
| 02548-88-77 | 12/3 | SJTW | Pink/Lime Green | 50 | Sleeve | 15A | 8 | 53 | 1.41 |
| 02548-88-NV | 12/3 | SJTW | Silver/Blue | 50 | Sleeve | 15A | 8 | 53 | 1.41 |
| 02548-88-3V | 12/3 | SJTW | Orange/Blue | 50 | Sleeve | 15A | 8 | 53 | 1.41 |
| 02548-88-P1 | 12/3 | SJTW | Purple/White | 50 | Sleeve | 15A | 8 | 53 | 1.41 |
| 02508-06-41 | 12/3 | SJTW | Red/White/Blue | 50 | Sleeve | 15A | 6 | 53 | 1.41 |
| 02549-88-54 | 12/3 | SJTW | Lime Green/Red | 100 | Sleeve | 15A | 4 | 52 | 1.41 |
| 02549-88-22 | 12/3 | SJTW | Yellow/Purple | 100 | Sleeve | 15A | 4 | 52 | 1.41 |
| 02549-88-52 | 12/3 | SJTW | Dark Green/Yellow | 100 | Sleeve | 15A | 4 | 52 | 1.41 |
| 02549-88-62 | 12/3 | SJTW | Blue/Yellow | 100 | Sleeve | 15A | 4 | 52 | 1.41 |
| 02549-88-64 | 12/3 | SJTW | Blue/Red | 100 | Sleeve | 15A | 4 | 52 | 1.41 |
| 02549-88-41 | 12/3 | SJTW | Red/White | 100 | Sleeve | 15A | 4 | 52 | 1.41 |
| 02549-88-77 | 12/3 | SJTW | Pink/Lime Green | 100 | Sleeve | 15A | 4 | 52 | 1.41 |
| 02549-88-NV | 12/3 | SJTW | Silver/Blue | 100 | Sleeve | 15A | 4 | 52 | 1.41 |
| 02549-88-3V | 12/3 | SJTW | Orange/Blue | 100 | Sleeve | 15A | 4 | 52 | 1.41 |
| 02549-88-P1 | 12/3 | SJTW | Purple/White | 100 | Sleeve | 15A | 4 | 52 | 1.41 |
| 02509-06-41 | 12/3 | SJTW | Red/White/Blue | 100 | Sleeve | 15A | 4 | 52 | 1.41 |
| 02648-00-54 | 10/3 | SJTW | Lime Green/Red | 50 | Disk | 15A | 4 | 46 | 1.41 |
| 02648-00-64 | 10/3 | SJTW | Blue/Red | 50 | Disk | 15A | 4 | 46 | 1.41 |
| 02649-00-54 | 10/3 | SJTW | Lime Green/Red | 100 | Disk | 15A | 3 | 68 | 1.41 |
| 02649-00-64 | 10/3 | SJTW | Blue/Red | 100 | Disk | 15A | 3 | 68 | 1.41 |

