



Dependable Power for Any Application

# Product Datasheet

190/200/208/220 X 380/400/416/440 Primary Volts - 110/220  
Secondary Volts - 1Ø - CE Marked  
Dry Type Distribution Transformer - Single Phase

Catalog #: TF279261S



## PRODUCT FEATURES

- UL listed, CSA certified
- Meet CSA C802.2 Efficiency
- Fully encapsulated core and coil
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

---

## BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

---

## UL STANDARD

UL 506

---

## CSA STANDARD

C22.2 No. 47

---

## CE

CE Marked

Acme Electric Warranty Card

---

## WARRANTY

[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

## GENERAL PRODUCT INFORMATION

|                       |                                   |
|-----------------------|-----------------------------------|
| kVA:                  | 2.00                              |
| Primary Voltage:      | 190/208/220/240 x 380/416/440/480 |
| Secondary Voltage:    | 120/240                           |
| Frequency:            | 50/60 Hz                          |
| Max Temperature Rise: | 115°C                             |
| UL Insulation Class:  | 180°C                             |

## PRODUCT MEASUREMENTS

|                  |              |
|------------------|--------------|
| Height (In./cm): | 13.00 (33.0) |
| Width (In./cm):  | 5.50 (14.0)  |
| Depth (In./cm):  | 5.13 (13.0)  |

## CONFIGURATION

|                     |                     |
|---------------------|---------------------|
| Construction Type:  | Encapsulated        |
| Mounting Type:      | Wall                |
| Knockouts (In./Cm): | 0.50-0.75 (1.3-1.9) |
| Weather Shield:     | WSA4                |
| Wiring Diagram:     | 64                  |

## PACKAGING

|                       |           |
|-----------------------|-----------|
| Ship Weight (Lbs/Kg): | 38 (17.2) |
|-----------------------|-----------|

## COMPLIANCES

|               |   |
|---------------|---|
| UL Standard:  | UL 506  |
| UL Listed:    | File E79947   |
| CSA Standard: | C22.2 No. 47  |
| CSA Listed:   | LR7357-32   |
| CE:           | CE Marked   |
| Warranty:     | Acme Electric Warranty Card<br><a href="http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf">www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf</a> |