


# LIQUIDATOR™ LIQUIDTIGHT FITTINGS



## Ordering Information

### Straight Connectors



| Malleable Iron |                        |                    |  |  |  |           | Aluminum                        |  |
|----------------|------------------------|--------------------|--|--|--|-----------|---------------------------------|--|
| Conduit Size   | Non-Insulated Cat. No. | Insulated Cat. No. | Non-Insulated with Aluminum Grounding Lug Cat. No. | Insulated with Aluminum Grounding Lug Cat. No. | Insulated with Copper Grounding Lug Cat. No. | Lug Size  | Non-Insulated Aluminum Cat. No. | Non-Insulated with Aluminum Grounding Lug Cat. No. |
| 3/8"           | LT38                   | LTB38              | LT38G  | LTB38G   | LTB38GC                                      | #4-#14    | LT38-SA                         | LT38G-SA   |
| 1/2"           | LT50                   | LTB50              | LT50G  | LTB50G   | LTB50GC                                      | #4-#14    | LT50-SA                         | LT50G-SA   |
| 3/4"           | LT75                   | LTB75              | LT75G  | LTB75G   | LTB75GC                                      | #4-#14    | LT75-SA                         | LT75G-SA   |
| 1"             | LT100                  | LTB100             | LT100G   | LTB100G  | LTB100GC                                     | #4-#14    | LT100-SA                        | LT100G-SA  |
| 1 1/4"         | LT125                  | LTB125             | LT125G   | LTB125G  | LTB125GC                                     | #4-#14    | LT125-SA                        | LT125G-SA  |
| 1 1/2"         | LT150                  | LTB150             | LT150G   | LTB150G  | LTB150GC                                     | #4-#14    | LT150-SA                        | LT150G-SA  |
| 2"             | LT200                  | LTB200             | LT200G   | LTB200G  | LTB200GC                                     | #4-#14    | LT200-SA                        | LT200G-SA  |
| 2 1/2"         | LT250                  | LTB250             | LT250G   | LTB250G  | LTB250GC                                     | #1/0-#8   | LT250-SA                        | LT250G-SA  |
| 3"             | LT300                  | LTB300             | LT300G   | LTB300G  | LTB300GC                                     | #1/0-#8   | LT300-SA                        | LT300G-SA  |
| 3 1/2"         | LT350                  | LTB350             | LT350G   | LTB350G  | LTB350GC                                     | #3/0-#6   | LT350-SA                        | LT350G-SA  |
| 4"             | LT400                  | LTB400             | LT400G   | LTB400G  | LTB400GC                                     | #3/0-#6   | LT400-SA                        | LT400G-SA  |
| 5"             | LT500                  | LTB500             | LT500G   | LTB500G  | —  | 250MCM-#6 | —                               | —  |
| 6"             | LT600                  | LTB600             | LT600G   | LTB600G  | —  | 250MCM-#6 | —                               | —  |

### 45° Angle Connectors



| Malleable Iron |                        |                    |  |  |  |          | Aluminum                        |  |
|----------------|------------------------|--------------------|--|--|--|----------|---------------------------------|--|
| Conduit Size   | Non-Insulated Cat. No. | Insulated Cat. No. | Non-Insulated with Aluminum Grounding Lug Cat. No. | Insulated with Aluminum Grounding Lug Cat. No. | Insulated with Copper Grounding Lug Cat. No. | Lug Size | Non-Insulated Aluminum Cat. No. |  |
| 3/8"           | LT3845                 | LTB3845            | LT3845G  | LTB3845G                                       | LTB3845GC                                    | #4-#14   | —                               |  |
| 1/2"           | LT5045                 | LTB5045            | LT5045G  | LTB5045G                                       | LTB5045GC                                    | #4-#14   | —                               |  |
| 3/4"           | LT7545                 | LTB7545            | LT7545G  | LTB7545G                                       | LTB7545GC                                    | #4-#14   | —                               |  |
| 1"             | LT10045                | LTB10045           | LT10045G   | LTB10045G                                      | LTB10045GC                                   | #4-#14   | —                               |  |
| 1 1/4"         | LT12545                | LTB12545           | LT12545G   | LTB12545G                                      | LTB12545GC                                   | #4-#14   | —                               |  |
| 1 1/2"         | LT15045                | LTB15045           | LT15045G   | LTB15045G                                      | LTB15045GC                                   | #4-#14   | —                               |  |
| 2"             | LT20045                | LTB20045           | LT20045G   | LTB20045G                                      | LTB20045GC                                   | #4-#14   | —                               |  |
| 2 1/2"         | LT25045                | LTB25045           | LT25045G   | LTB25045G                                      | LTB25045GC                                   | #1/0-#8  | —                               |  |
| 3"             | LT30045                | LTB30045           | LT30045G   | LTB30045G                                      | LTB30045GC                                   | #1/0-#8  | —                               |  |
| 3 1/2"         | LT35045                | LTB35045           | LT35045G   | LTB35045G                                      | LTB35045GC                                   | #3/0-#6  | —                               |  |
| 4"             | LT40045                | LTB40045           | LT40045G   | LTB40045G                                      | LTB40045GC                                   | #3/0-#6  | —                               |  |

### 90° Angle Connectors



| Malleable Iron |                        |                    |  |  |  |          | Aluminum                        |  |
|----------------|------------------------|--------------------|--|--|--|----------|---------------------------------|--|
| Conduit Size   | Non-Insulated Cat. No. | Insulated Cat. No. | Non-Insulated with Aluminum Grounding Lug Cat. No. | Insulated with Aluminum Grounding Lug Cat. No. | Insulated with Copper Grounding Lug Cat. No. | Lug Size | Non-Insulated Aluminum Cat. No. | Non-Insulated with Aluminum Grounding Lug Cat. No. |
| 3/8"           | LT3890                 | LTB3890            | LT3890G  | LTB3890G                                       | LTB3890GC                                    | #4-#14   | LT3890-SA                       | LT3890G-SA   |
| 1/2"           | LT5090                 | LTB5090            | LT5090G  | LTB5090G                                       | LTB5090GC                                    | #4-#14   | LT5090-SA                       | LT5090G-SA   |
| 3/4"           | LT7590                 | LTB7590            | LT7590G  | LTB7590G                                       | LTB7590GC                                    | #4-#14   | LT7590-SA                       | LT7590G-SA   |
| 1"             | LT10090                | LTB10090           | LT10090G   | LTB10090G                                      | LTB10090GC                                   | #4-#14   | LT10090-SA                      | LT10090G-SA  |
| 1 1/4"         | LT12590                | LTB12590           | LT12590G   | LTB12590G                                      | LTB12590GC                                   | #4-#14   | LT12590-SA                      | LT12590G-SA  |
| 1 1/2"         | LT15090                | LTB15090           | LT15090G   | LTB15090G                                      | LTB15090GC                                   | #4-#14   | LT15090-SA                      | LT15090G-SA  |
| 2"             | LT20090                | LTB20090           | LT20090G   | LTB20090G                                      | LTB20090GC                                   | #4-#14   | LT20090-SA                      | LT20090G-SA  |
| 2 1/2"         | LT25090                | LTB25090           | LT25090G   | LTB25090G                                      | LTB25090GC                                   | #1/0-#8  | —                               | —  |
| 3"             | LT30090                | LTB30090           | LT30090G   | LTB30090G                                      | LTB30090GC                                   | #1/0-#8  | —                               | —  |
| 3 1/2"         | LT35090                | LTB35090           | LT35090G   | LTB35090G                                      | LTB35090GC                                   | #3/0-#6  | —                               | —  |
| 4"             | LT40090                | LTB40090           | LT40090G   | LTB40090G                                      | LTB40090GC                                   | #3/0-#6  | —                               | —  |