

# HazMax Pinnacle/al

## SPARE PARTS

Part No.	Description	Part No.	Description
FX5350	BALLAST 120-277V AC 50/60HZ, 1 x 14, F14T5	FX3568	LAMP, 24w, F24T5HO
FX5350	BALLAST 120-277V AC 50/60HZ, 1 x 28, F28T5	FX3567	LAMP, 54w, F54T5HO
FX5307	BALLAST 120-277V AC 50/60HZ, 1 x 24, F24T5HO	FX3577	LAMP, 54w, Long Life F54T5HO
FX5305	BALLAST 120-277V AC 50/60HZ, 1 x 54, F54T5HO	FX3528	LAMP, 17w, F17T8
FX5174	BALLAST 120-277V AC 50/60HZ, 1 x 17, F17T8	FX3527	LAMP, 32w, F32T8
FX5221	BALLAST 120-277V AC 50/60HZ, 1 x 32, F32T8	FX3565	LAMP, 44w, F48T8HO
FX5349	BALLAST 120-277V AC 50/60HZ, 1 x 44, F48T8HO	FX3507	LAMP, 35w, F24T12HO
FX5334	BALLAST 120-277V AC 50/60HZ, 1 x 35, F24T12HO	FX3505	LAMP, 60w, F48T12HO
FX5334	BALLAST 120-277V AC 50/60HZ, 1 x 60, F48T12HO	FX3533	LAMP, 40w CF, FT40 2G11
FX5272	BALLAST 120-277V AC 50/60HZ, 1 X 40 CF, FT40 2G11	103-2000	LENS & FRAME ASSEMBLY, 2 ft. models
FX5350	BALLAST 120-277V AC 50/60HZ, 2 x 14, F14T5	103-2001	DOOR FRAME ONLY, 2 ft. models
FX5350	BALLAST 120-277V AC 50/60HZ, 2 x 28, F28T5	103-2100	LENS ONLY, (acrylic), for 2 ft. models
FX5307	BALLAST 120-277V AC 50/60HZ, 2 x 24, F24T5HO	103-2200	LENS GASKET, 2 ft. models
FX5305	BALLAST 120-277V AC 50/60HZ, 2 X 54, F54T5HO	103-2300	REFLECTOR, 2 ft. models
FX5340	BALLAST 120-277V AC 50/60HZ, 2 x 17, F17T8	035-1060	LATCH ASSEMBLY
FX5340	BALLAST 120-277V AC 50/60HZ, 2 x 32, F32T8	103-4000	LENS & FRAME ASSEMBLY, 4 ft. models
FX5349	BALLAST 120-277V AC 50/60HZ, 2 x 44, F48T8HO	103-4001	DOOR FRAME ONLY, 4 ft. models
FX5334	BALLAST 120-277V AC 50/60HZ, 2 x 35, F24T12HO	103-4100	LENS ONLY (acrylic), 4 ft. models
FX5334	BALLAST 120-277V AC 50/60HZ, 2 x 60, F48T12HO	103-4200	LENS GASKET, 4 ft. models
FX5272	BALLAST 120-277V AC 50/60HZ, 2 x 40, FT40 2G11	103-4300	REFLECTOR, 4 ft. models
FX5128HDU	EMERGENCY BATTERY BACKUP BALLAST, EM1/EMT1, 120v-277v, CF, T8, T8HO & T12HO	758-0523	LAMP HOLDER, HO T8 & T12
FX5346HDU	EMERGENCY BATTERY BACKUP BALLAST, EM1/EMT1, 120v-277v, T5 & T5HO	752-6051	LAMP HOLDER, 2G11, 4 Pin
FX3573	LAMP, 14w, F14T5	754-7102	LAMP HOLDER, T12 & T8, Bi-Pin
FX3574	LAMP, 28w, F28T5	754-0005	LAMP HOLDER, T5 HO, fixed & spring set