

**Energy Saver**  
 Isolated  
 High-Efficiency TP1

Three-Phase 60 Hz 150°C Rise Aluminum										GO-66A
Input Voltage	Output Voltage	KVA	Height (in)	Width (in)	Depth (in)	Taps	Wiring Diagram No. <sup>1</sup>	Approx. Net Weight (Lbs.)	Product Number	List Price
480 Volts	208Y/120 V	15	27.38	19	16.57	6	18	240	9T83B3871	\$3682.00
480 Volts	208Y/120 V	30	32.25	24	18.07	6	18	333	9T83B3872	\$4503.00
480 Volts	208Y/120 V	45	32.25	24	18.07	6	18	379	9T83B3873	\$5575.00
480 Volts	208Y/120 V	75	35.75	32	23.69	6	18	527	9T83B3874	\$7950.00
480 Volts	208Y/120 V	112.5	40	32	23.69	6	18	659	9T83B3875	\$9998.00
480 Volts	208Y/120 V	150	37.3	29.5	28.5	6	18	845	9T40G0006	\$12733.00
480 Volts	208Y/120 V	225	37.3	29.5	28.5	6	18	845	9T40G0007	\$16244.00
480 Volts	208Y/120 V	300	40.9	34.8	25.6	6	18	1020	9T40G0008	\$26595.00
480 Volts	208Y/120 V	500	45.4	38.5	33.6	6	18	1585	9T40G0009	\$38930.00
480 Volts	208Y/120 V	750	57.5	47.5	40.0	6	18	3250	9T40G0010	\$69350.00

Three-Phase 60 Hz 115°C Rise Aluminum										GO-66A
Input Voltage	Output Voltage	KVA	Height (in)	Width (in)	Depth (in)	Taps	Wiring Diagram No. <sup>1</sup>	Approx. Net Weight (Lbs.)	Product Number	List Price
480 Volts	208Y/120 V	15	27.38	19	16.57	6	18	240	9T83B3871G15	\$7101.00
480 Volts	208Y/120 V	30	32.25	24	18.07	6	18	333	9T83B3872G15	\$7539.00
480 Volts	208Y/120 V	45	32.25	24	18.07	6	18	379	9T83B3873G15	\$10270.00
480 Volts	208Y/120 V	75	35.75	32	23.69	6	18	527	9T83B3874G15	\$12892.00
480 Volts	208Y/120 V	112.5	40	32	23.69	6	18	659	9T83B3875G15	\$15950.00
480 Volts	208Y/120 V	150	37.3	29.5	28.5	6	18	845	9T40G0006G51	\$23702.00
480 Volts	208Y/120 V	225	40.9	34.8	25.6	6	18	1020	9T40G0007G51	\$37691.00
480 Volts	208Y/120 V	300	45.4	38.5	33.6	6	18	1585	9T40G0008G51	\$43481.00
480 Volts	208Y/120 V	500	57.5	47.5	40.0	6	18	3250	9T40G0009G51	\$56810.00
480 Volts	208Y/120 V	750	57.5	47.5	40.0	6	18	3250	9T40G0010G51	\$79753.00

Three-Phase 60 Hz 80°C Rise Aluminum										GO-66A
Input Voltage	Output Voltage	KVA	Height (in)	Width (in)	Depth (in)	Taps	Wiring Diagram No. <sup>1</sup>	Approx. Net Weight (Lbs.)	Product Number	List Price
480 Volts	208Y/120 V	15	32.25	24	18.07	6	18	333	9T83B3871G80	\$7719.00
480 Volts	208Y/120 V	30	32.25	24	18.07	6	18	379	9T83B3872G80	\$8194.00
480 Volts	208Y/120 V	45	35.75	32	23.69	6	18	527	9T83B3873G80	\$11163.00
480 Volts	208Y/120 V	75	40	32	23.69	6	18	659	9T83B3874G80	\$14013.00
480 Volts	208Y/120 V	112.5	37.3	29.5	28.5	6	18	845	9T40G0005G81	\$17337.00
480 Volts	208Y/120 V	150	40.9	34.8	25.6	6	18	1020	9T40G0006G81	\$25768.00
480 Volts	208Y/120 V	225	45.4	38.5	33.6	6	18	1585	9T40G0007G81	\$40968.00
480 Volts	208Y/120 V	300	45.4	38.5	33.6	6	18	1585	9T40G0008G81	\$47262.00
480 Volts	208Y/120 V	500	57.5	47.5	40.0	6	18	3250	9T40G0009G81	\$61750.00

<sup>1</sup>See page 8-17 for wiring diagrams.

TRANSFORMERS



distributed by AA Electric 1-800-237-8274 www.a-aelectric.com