

C-WM-A-WLHR Series

LED Wall Mount

Replaces 100W / 120W Incandescent

C-LITE
LED LIGHTING BY CREE



POWERFUL, EFFICIENT & LONG LASTING LIGHT

RECOMMENDED USE

- Security
- Stairways
- Perimeter lighting

INPUT VOLTAGE

- 120V Operation with built-in photocell


CERTIFICATIONS:



US: c-lite.com

T (800) 236-6800 F (262) 504-5415

C-WM-A-WLHR Series



Series overview

DIMENSIONS	PRODUCT WEIGHT	MOUNTING HEIGHT	SPACING
4" D x 5-3/4" W x 9" H	2.0 lbs.	8 to 12 feet	N/A


Fixture Specifications

HOUSING	Polycarbonate housing in medium bronze or white with heavy-duty aluminum mounting plate
LENS ASSEMBLY	UV-stabilized polycarbonate prismatic refractor
MOUNTING	1/2" NPT tapped knockout on bottom for conduit entry • Knockout provided on back of housing for 1/2" conduit entry or mounts over 4" square or octagonal junction box

Electrical Performance

OPERATING MINIMUM	LIFESPAN <small>L₇₀ AT 25°C (77°F)</small>	POWER FACTOR	TOTAL HARMONIC DISTORTION	DIMMABLE
-40°C (-40°F)	172,000 Hours (22W) 118,000 Hours (14W)	> 0.95	< 20%	No
INPUT VOLTAGE	120V	208V	240V	277V
CURRENT DRAW (Amps)	0.17A	N/A	N/A	N/A

CORRELATED COLOR TEMPERATURE (CCT)



Warranty and Certifications

Warranty	UL Listed	Energy Star
5-Year Limited*	Wet Locations	N/A

Output Specifications

SKU	Light Output	Color Temp (see chart)	Power Consumption	Color Accuracy	Replaces
C-WM-A-WLHR-10L-40K-MB	1,000 Lumens	Neutral White (4000K)	14W	≥ 70 CRI	100W Incandescent
C-WM-A-WLHR-10L-40K-WH	1,000 Lumens	Neutral White (4000K)	14W	≥ 70 CRI	100W Incandescent
C-WM-A-WLHR-12L-40K-MB	1,200 Lumens	Neutral White (4000K)	22W	≥ 70 CRI	120W Incandescent
C-WM-A-WLHR-12L-40K-WH	1,200 Lumens	Neutral White (4000K)	22W	≥ 70 CRI	120W Incandescent

© 2017 Cree, Inc. and/or one of its subsidiaries. All rights reserved. For informational purposes only. Content is subject to change. Patent www.cree.com/patents. The CREE LEDs logo, C-LITE™ and the C-LITE logo are trademarks of Cree, Inc. The UL logo is a registered trademark of UL LLC.
*See lighting.cree.com/warranty for details. Revision Date: V1 05/03/2017