

**Energy Saver**  
**Isolated**  
**High-Efficiency TP1**

Three-Phase 60 Hz 150°C Rise Copper										GO-66A
Input Voltage	Output Voltage	KVA	Height (in)	Width (in)	Depth (in)	Taps	Wiring Diagram No. <sup>1</sup>	Approx. Net Weight (Lbs.)	Product Number	List Price
480 Volts	208Y/120 V	15	27.38	19	16.57	6	18	240	9T83C9871	\$6175.00
480 Volts	208Y/120 V	30	32.25	24	18.07	6	18	372	9T83C9872	\$6840.00
480 Volts	208Y/120 V	45	32.25	24	18.07	6	18	453	9T83C9873	\$9785.00
480 Volts	208Y/120 V	75	35.75	32	23.69	6	18	643	9T83C9874	\$12825.00
480 Volts	208Y/120 V	112.5	40	32	23.69	6	18	659	9T83C9875	\$17575.00
480 Volts	208Y/120 V	150	37.3	29.5	28.5	6	18	976	9T45G0006	\$22419.00
480 Volts	208Y/120 V	225	37.3	29.5	28.5	6	18	976	9T45G0007	\$34899.00
480 Volts	208Y/120 V	300	40.9	34.8	25.6	6	18	1160	9T45G0008	\$40659.00
480 Volts	208Y/120 V	500	45.4	38.5	33.6	6	18	1780	9T45G0009	\$52819.00
480 Volts	208Y/120 V	750	57.5	47.5	40.0	6	18	4450	9T45G0010	\$79800.00

Three-Phase 60 Hz 115°C Rise Copper										GO-66A
Input Voltage	Output Voltage	KVA	Height (in)	Width (in)	Depth (in)	Taps	Wiring Diagram No. <sup>1</sup>	Approx. Net Weight (Lbs.)	Product Number	List Price
480 Volts	208Y/120 V	15	27.38	19	16.57	6	18	240	9T83C9871G15	\$7101.00
480 Volts	208Y/120 V	30	32.25	24	18.07	6	18	372	9T83C9872G15	\$7866.00
480 Volts	208Y/120 V	45	32.25	24	18.07	6	18	453	9T83C9873G15	\$11253.00
480 Volts	208Y/120 V	75	35.75	32	23.69	6	18	643	9T83C9874G15	\$14750.00
480 Volts	208Y/120 V	112.5	40	32	23.69	6	18	659	9T83C9875G15	\$20211.00
480 Volts	208Y/120 V	150	37.3	29.5	28.5	6	18	976	9T45G0006G51	\$25782.00
480 Volts	208Y/120 V	225	40.9	34.8	25.6	6	18	1160	9T45G0007G51	\$40203.00
480 Volts	208Y/120 V	300	45.4	38.5	33.6	6	18	1780	9T45G0008G51	\$46758.00
480 Volts	208Y/120 V	500	57.5	47.5	40.0	6	18	4450	9T45G0009G51	\$60742.00
480 Volts	208Y/120 V	750	57.5	47.5	40.0	6	18	4450	9T45G0010G51	\$91770.00

Three-Phase 60 Hz 80°C Rise Copper										GO-66A
Input Voltage	Output Voltage	KVA	Height (in)	Width (in)	Depth (in)	Taps	Wiring Diagram No. <sup>1</sup>	Approx. Net Weight (Lbs.)	Product Number	List Price
480 Volts	208Y/120 V	15	32.25	24	18.07	6	18	372	9T83C9871G80	\$7719.00
480 Volts	208Y/120 V	30	32.25	24	18.07	6	18	453	9T83C9872G80	\$8550.00
480 Volts	208Y/120 V	45	35.75	32	23.69	6	18	643	9T83C9873G80	\$12231.00
480 Volts	208Y/120 V	75	40	32	23.69	6	18	659	9T83C9874G80	\$16031.00
480 Volts	208Y/120 V	112.5	37.3	29.5	28.5	6	18	976	9T45G0005G81	\$21968.00
480 Volts	208Y/120 V	150	37.3	29.5	28.5	6	18	976	9T45G0006G81	\$28024.00
480 Volts	208Y/120 V	225	40.9	34.8	25.6	6	18	1160	9T45G0007G81	\$43699.00
480 Volts	208Y/120 V	300	45.4	38.5	33.6	6	18	1780	9T45G0008G81	\$50824.00
480 Volts	208Y/120 V	500	57.5	47.5	40.0	6	18	4450	9T45G0009G81	\$66025.00
480 Volts	208Y/120 V	750	57.5	47.5	40.0	6	18	4450	9T45G0010G81	\$99750.00

<sup>1</sup>See page 8-17 for wiring diagrams.

Publications and Reference: See Section 21 for a list of additional product-related publications



distributed by AA Electric 1-800-237-8274 www.a-aelectric.com