

Encapsulated Cat #	Non-Encapsulated Cat #	Phase	Freq	CoilMat'l	kVA	Primary Voltage	Secondary Voltage	TempRise	Ambient Temp	Frame Size	Fuse Holder	Leads Out/Screw Terminals
9T58K2813	9T58R2813	1	60	CU	1.50	240x480	120/240	100	40	14225	NONE	Screw Terminals
9T58K2814	9T58R2814	1	60	CU	2.00	240x480	120/240	100	40	14300	NONE	Screw Terminals
9T58K2815	9T58R2815	1	60	CU	3.00	240x480	120/240	100	40	14475	NONE	Screw Terminals
9T58K2823	9T58R2823	1	60	CU	0.08	600	120/240	55	40	6125	NONE	Screw Terminals
9T58K2824	9T58R2824	1	60	CU	0.10	600	120/240	55	40	8100	NONE	Screw Terminals
9T58K2826	9T58R2826	1	60	CU	0.20	600	120/240	80	40	8175	NONE	Screw Terminals
9T58K2827	9T58R2827	1	60	CU	0.25	600	120/240	80	40	8200	NONE	Screw Terminals
9T58K2828	9T58R2828	1	60	CU	0.30	600	120/240	100	40	8200	NONE	Screw Terminals
9T58K2830	9T58R2830	1	60	CU	0.50	600	120/240	80	40	10225	NONE	Screw Terminals
9T58K2831	9T58R2831	1	60	CU	0.75	600	120/240	100	40	12225	NONE	Screw Terminals
9T58K2832	9T58R2832	1	60	CU	1.00	600	120/240	115	40	12300	NONE	Screw Terminals
9T58K2833	9T58R2833	1	60	CU	1.50	600	120/240	100	40	14225	NONE	Screw Terminals
9T58K2834	9T58R2834	1	60	CU	2.00	600	120/240	100	40	14300	NONE	Screw Terminals
9T58K2835	9T58R2835	1	60	CU	3.00	600	120/240	100	40	14475	NONE	Screw Terminals
9T58K2873	9T58R2873	1	60	CU	0.05	120x240	12/24	55	40	6100	NONE	Screw Terminals
9T58K2874	9T58R2874	1	60	CU	0.08	120x240	12/24	55	40	6125	NONE	Screw Terminals
9T58K2875	9T58R2875	1	60	CU	0.10	120x240	12/24	55	40	8100	NONE	Screw Terminals
9T58K2876	9T58R2876	1	60	CU	0.15	120x240	12/24	55	40	8150	NONE	Screw Terminals
9T58K2877	9T58R2877	1	60	CU	0.20	120x240	12/24	80	40	8175	NONE	Screw Terminals
9T58K2878	9T58R2878	1	60	CU	0.25	120x240	12/24	100	40	8200	NONE	Screw Terminals
9T58K2879	9T58R2879	1	60	CU	0.30	120x240	12/24	100	40	8200	NONE	Screw Terminals
9T58K2890	9T58R2890	1	60	CU	0.08	120x240	16/32	55	40	8175	NONE	Screw Terminals
9T58K2892	9T58R2892	1	50	CU	0.10	115/120	13.4	115	40	8200	NONE	Screw Terminals
9T58K2893	9T58R2893	1	60	CU	0.20	120x240	16/32	80	40	8175	NONE	Screw Terminals
9T58K2907	9T58R2907	1	60	CU	0.10	120x240	120/240	55	40	8100	NONE	Screw Terminals
9T58K2909	9T58R2909	1	60	CU	0.20	120x240	120/240	80	40	8175	NONE	Screw Terminals
9T58K2911	9T58R2911	1	60	CU	0.30	120x240	120/240	100	40	8200	NONE	Screw Terminals
9T58K2913	9T58R2913	1	60	CU	0.50	120x240	120/240	80	40	10225	NONE	Screw Terminals
9T58K2914	9T58R2914	1	60	CU	0.75	120x240	120/240	100	40	12225	NONE	Screw Terminals
9T58K2915	9T58R2915	1	60	CU	1.00	120x240	120/240	115	40	12300	NONE	Screw Terminals
9T58K2917	9T58R2917	1	60	CU	2.00	120x240	120/240	100	40	14300	NONE	Screw Terminals
9T58K2918	9T58R2918	1	60	CU	3.00	120x240	120/240	115	40	14475	NONE	Screw Terminals
9T58K2930	9T58R2930	1	50	CU	0.50	240x480	120/240	115	40	10225	NONE	Screw Terminals
9T58K2931	9T58R2931	1	50	CU	0.75	240x480	120/240	100	40	12300	NONE	Screw Terminals
9T58K2932	9T58R2932	1	50	CU	1.00	240x480	120/240	100	40	14225	NONE	Screw Terminals
9T58K2933	9T58R2933	1	50	CU	1.50	240x480	120/240	100	40	14300	NONE	Screw Terminals