



CORDLESS POWER TOOLS

GUARANTEED TOUGH.

NAILERS



18V Cordless 1-1/4" - 2-1/2" 15 Gauge 34° Angled Finish Nailer Kit

SPECIFICATIONS	DC628K
Volts	18V
Operating Mode	Bump & Sequential
Nailing Rate	4-5 nails/sec
Nail Diameter/Type	15ga. DA type gauge
Mag. Angle/Capacity	34°/110 nails
Nail Length Capacity	1-1/4" - 2-1/2"
Magazine Loading	Rear-load
Integrated Belt Hook	Yes
Tool-Free Jam Clearing	Yes
Tool-Free Depth Adj.	Yes
Weight	89 lbs
Charger/Batteries	1 Hour Charger / (1) 18V XRP™



18V Cordless 1-1/4" - 2-1/2" 16 Gauge 20° Angled Finish Nailer Kit



18V Cordless 1-1/4" - 2-1/2" 16 Gauge Straight Finish Nailer Kit



18V Cordless 5/8" - 2" 18 Gauge Straight Brad Nailer Kit



18V Cordless 5/8" - 2" 18 Gauge Straight Brad Nailer (Tool Only)

SPECIFICATIONS	DC618K	DC616K	DC608K	DC608B
Volts	18V	18V	18V	18V
Operating Mode	Bump & Sequential	Bump & Sequential	Bump & Sequential	Bump & Sequential
Nailing Rate	4-5 nails/sec	4-5 nails/sec	4-5 nails/sec	4-5 nails/sec
Nail Diameter/Type	16 gauge	16 gauge	18 gauge	18 gauge
Mag. Angle/Capacity	20°/110 nails	Straight/110 nails	Straight/110 nails	Straight/110 nails
Nail Length Capacity	1-1/4" - 2-1/2"	1-1/4" - 2-1/2"	5/8" - 2"	5/8" - 2"
Magazine Loading	Rear-load	Rear-load	Side-load	Side-load
Integrated Belt Hook	Yes	Yes	Yes	Yes
Tool-Free Jam Clearing	Yes	Yes	Yes	Yes
Tool-Free Depth Adj.	Yes	Yes	Yes	Yes
Weight	8.5 lbs	8.5 lbs	7.4 lbs	8.4lbs (tool only)
Charger/Batteries	1 Hour Charger / (1) 18V XRP™	1 Hour Charger / (1) 18V XRP™	1 Hour Charger / (1) 18V XRP™	Sold Separately

SEARS



18V Cordless 18 Gauge Off-Set Shear (Tool Only)



18V Cordless 18 Gauge Swivel Head and Shear (Tool Only)

SPECIFICATIONS	DC495B	DC490B
Volts	18V	18V
Stroke/Min	0-2,300 spm	0-2,300 spm
Max. Cutting Radius	1"	5.5"
Capacity in Steel	18 Gauge	18 Gauge
Weight	3.7 lbs (tool only)	3.7 lbs (tool only)
Charger/Batteries	Sold Separately	Sold Separately
Includes	Blade wrench	Blade wrench

CUT-OUT TOOL



18V Cordless Cut-Off Tool (Tool Only)

SPECIFICATIONS	DC550B
Volts	18V
No Load Speed	28,000 rpm
Coil Diameter	1/4", 1/8"
Adjustable Guide	Yes
Weight	2.1 lbs (tool only)
Charger/Batteries	Sold Separately
Includes	(1) Core Purpose Bit, (1) Drywall Cutting Bit, 1/4" & 1/8" Coils