



CORDLESS POWER TOOLS

GUARANTEED TOUGH.

HAMMER DRILLS



1/2" (13mm) 36V Cordless Li-Ion Hammerdrill/Drill/Driver Kit



20V MAX* Lithium Ion Premium 3-Speed Hammerdrill Kit (3.0Ah)



1/2" (13mm) 18V Cordless XRP™ Li-Ion Hammerdrill/Drill/Driver Kit



20V MAX* Lithium Ion Compact Hammerdrill Kit (1.5 Ah)

SPECIFICATIONS	DC90 1KL	DCD98 5L2	DCD97 0KL	DCD78 3C2
Volts	36V	20V MAX*	18V	20V MAX*
Max Power	750 UWO	585 UWO	450 UWO	350 UWO
# of Speed Settings	3	3	3	2
No Load Speed	-	-	-	0-600/0-2,000 rpm
Max RPM	0-40 0/0-1,200/0-1,800 rpm	0-575/0-1,350/0-2,000 rpm	0-500/0-1,250/0-2,000 rpm	2,000 rpm
Max BPM	0-8,800/0-20,400/0-27,200 bpm	0-9,775/0-22,950/0-34,000 bpm	0-8,500/0-21,250/0-34,000 bpm	0-10,200/0-34,000 bpm
Chuck Size	1/2"	1/2"	1/2"	1/2"
Chuck Type	Metals, self-tightening	Metal, ratcheting	Metal, ratcheting	Metal, ratcheting
Weight	6.75 lbs	5.2 lbs	5.25 lbs	3.5 lbs
Charger/Batteries	1 Hour Charger / (2) 36V Lithium Ion	Fast Charger / (2) 20V MAX* Lithium Ion 3.0Ah	1 Hour NiCd/MMH/Li-Ion charger / (2) 18V XRP™ Lithium Ion	Fast Charger / (2) 20V MAX* Lithium Ion 1.5Ah
Includes	360° side handle	360° side handle	360° side handle	On-board bit lip holder & belt hook



1/2" (13mm) 18V Cordless XRP™ Hammerdrill/Drill/Driver Kit



1/2" (13mm) 18V Cordless XRP™ Hammerdrill/Drill/Driver Kit



1/2" (13mm) 18V XRP™ Hammerdrill/Drill/Driver (Tool Only)



18V 1/2" (13mm) Cordless Compact Hammerdrill Kit

SPECIFICATIONS	DCD959 5KX/VX**	DCD950 5KX/VX**	DCD950 8	DC725 8A
Volts	18V	18V	18V	18V
Max Power	420 UWO	450 UWO	450 UWO	410 UWO
# of Speed Settings	3	3	3	2
Max RPM	0-450/0-1,450/0-2,000 rpm	0-500/0-1,250/0-2,000 rpm	0-500/0-1,250/0-2,000 rpm	0-500/0-1,700 rpm
Max BPM	0-7650/0-24,650/0-34000 bpm	0-8,500/0-21,250/0-34,000 bpm	0-8,500/0-21,250/0-34,000 bpm	0-8,500/0-29,000 bpm
Chuck Size	1/2"	1/2"	1/2"	1/2"
Chuck Type	Metal, ratcheting	Metal, ratcheting	Metal, ratcheting	Metal, ratcheting
Weight	6.0 lbs	6.25 lbs	3.9 lbs (tool only)	4.9 lbs
Charger/Batteries	1 Hour Charger / (2) 18V XRP™	1 Hour Charger / (2) 18V XRP™	Sold Separately	1 Hour Charger / (2) 18V
Includes	360° side handle	360° side handle	360° side handle	-

**Vehicle charger



1/2" (13mm) 18V Cordless Compact Li-Ion Hammerdrill Kit



1/2" (13mm) 18V Cordless Compact Hammerdrill (Tool Only)



14.4V 1/2" (13mm) Cordless XRP™ Hammerdrill/Drill/Driver Kit

SPECIFICATIONS	DCD77 5KL	DCD77 5B	DCD930 5KX/VX**
Volts	18V	18V	14.4V
Max Power	350 UWO	350 UWO	325 UWO
# of Speed Settings	2	2	3
Max RPM	0-500/0-1,700 rpm	0-500/0-1,700 rpm	0-425/0-1,200/0-1,800 rpm
Max BPM	0-8,500/0-29,000 bpm	0-8,500/0-29,000 bpm	0-7225/0-20,400/0-30600 bpm
Chuck Size	1/2"	1/2"	1/2"
Chuck Type	Metal, ratcheting	Metal, ratcheting	Metal, ratcheting
Weight	4.1 lbs (tool only)	3.1 lbs (tool only)	5.75 lbs
Charger/Batteries	30-Minute Charger / (2) 18V Compact Lithium-Ion	Sold Separately	1 Hour Charger / (2) 14.4V XRP™
Includes	-	-	360° side handle

**Vehicle charger