

**DEWALT**

**HEAVY-DUTY POWER TOOLS**

**GUARANTEED TOUGH.**



**HAMMERDRILL/DRILL/DRIVERS**



1/2" (13mm) 36V Cordless Hammerdrill/Drill/Driver Kit

SPECIFICATIONS	DC900KL
Voltage	36V
Max. Power	750 UWO
# of Speed Settings	3
Max. RPM	0-400/0-1,200/0-1,600
Max. BPM	0-6,800/0-20,400/0-27,200
Chuck Size	1/2"
Chuck Type	Self-tightening
Tool Weight	6.9 lbs
Charger/Batteries	1 hour / (2) 36V
Includes	360° side handle

**XRP™ HAMMERDRILLS**



1/2" (13mm) 18V Cordless Hammerdrill/Drill/Driver Kit    1/2" (13mm) 18V Cordless Hammerdrill/Drill/Driver Kit    1/2" (13mm) 14.4V Cordless Hammerdrill/Drill/Driver Kit    1/2" (13mm) 14.4V Cordless Hammerdrill/Drill/Driver Kit

SPECIFICATIONS	DC925KA/VA*	DC926KA/VA*	DC935KA/VA*	DC936KA/VA*
Voltage	18V	18V	14.4V	14.4V
Max. Power	510 UWO	510 UWO	335 UWO	335 UWO
# of Speed Settings	3	3	3	3
Max. RPM	0-450/0-1,500/0-2,000	0-450/0-1,500/0-2,000	0-450/0-1,450/0-1,800	0-450/0-1,450/0-1,800
Max. BPM	0-7,650/0-25,500/0-34,000	0-7,650/0-25,500/0-34,000	0-7,650/0-24,650/0-30,600	0-7,650/0-24,650/0-30,600
Chuck Size	1/2"	1/2"	1/2"	1/2"
Chuck Type	Self-tightening	Self-tightening	Self-tightening	Self-tightening
Tool Weight	6.2 lbs	6.2 lbs	5.4 lbs	5.4 lbs
Charger/Batteries	1 hour / (2) 18V XRP™	1 hour / (2) 18V XRP™	1 hour / (2) 14.4V XRP™	1 hour / (2) 14.4V XRP™
Includes	360° side handle	360° side handle		

**XRP™ DRILL/DRIVERS**



1/2" (13mm) 18V Cordless Drill/Driver Kit    1/2" (13mm) 14.4V Cordless Drill/Driver Kit    1/2" (13mm) 12V Cordless Drill/Driver Kit

SPECIFICATIONS	DC920KA	DC930KA	DC940KA
Voltage	18V	14.4V	12V
Max. Power	510 UWO	335 UWO	290 UWO
# of Speed Settings	3	3	3
Max. RPM	0-450/0-1,500/0-2,000	0-450/0-1,450/0-1,800	0-450/0-1,450/0-1,800
Chuck Size	1/2"	1/2"	1/2"
Chuck Type	metal, single sleeve ratcheting	metal, single sleeve ratcheting	metal, single sleeve ratcheting
Tool Weight	6.0 lbs	5.3 lbs	5.0 lbs
Charger/Batteries	1 hour / (2) 18V XRP™	1 hour / (2) 14.4V XRP™	1 hour / (2) 12V XRP™
Includes	360° side handle		

**COMPACT POWER™**



1/2" (13mm) 18V Cordless Compact Drill/Driver Kit    1/2" (13mm) 14.4V Cordless Compact Drill/Driver Kit    3/8" (10mm) 12V Cordless Compact Drill/Driver Kit    3/8" (10mm) 9.6V Cordless Compact Drill/Driver Kit

SPECIFICATIONS	DC759KA	DC728KA	DC727KA/VA*	DC750KA
Voltage	18V	14.4V	12V	9.6V
Max. Power	380 UWO	270 UWO	230 UWO	130 UWO
# of Speed Settings	2	2	2	2
Max. RPM	0-450/0-1,500	0-400/0-1,400	0-400/0-1,400	0-300/0-1,100
Chuck Size	1/2"	1/2"	3/8"	3/8"
Chuck Type	plastic, single sleeve ratcheting	plastic, single sleeve ratcheting	plastic, single sleeve ratcheting	plastic, single sleeve ratcheting
Tool Weight	5.2 lbs	4.7 lbs	3.9 lbs	3.4 lbs
Charger/Batteries	1 hour / (2) 18V	1 hour / (2) 14.4V	1 hour / (2) 12V	1 hour / (2) 9.6V
Includes	double-ended screwdriver bit	double-ended screwdriver bit	double-ended screwdriver bit	double-ended screwdriver bit

\*Comes with 1 hour vehicle charger

[www.Dewalt.com](http://www.Dewalt.com)

1-800-4 DEWALT

<PREVIOUS

1  
NEXT>