



HEAVY-DUTY POWER TOOLS

GUARANTEED TOUGH.

CORDLESS COMBO KITS



36V Cordless 4-Tool Combo Kit 36V Cordless 2-Tool Combo Kit 36V Cordless 2-Tool Combo Kit 18V Cordless 4-Tool Combo Kit 18V Cordless 4-Tool Combo Kit

SPECIFICATIONS	DCX6401	DCX6200	DCX6210	DC4PAKA	DC4MEGA
Voltage	36V	36V	36V	18V	18V
Hammerdrill/Drill/Driver	DC900	DC900	DC900	DC925	DC925
Rotary Hammer	-	-	-	DC212	DC212
Circular Saw	DC300 (7-1/4")	DC300 (7-1/4")	-	DC390 (6-1/2")	-
Reciprocating Saw	DC305	-	DC305	DC385	DC385
Flexible Floodlight	DC509	-	-	DW919	DW919
Charger/Batteries	1 hour / (2) 36V	1 hour / (2) 36V	1 hour / (2) 36V	1 hour / (2) 18V XRP™	1 hour / (2) 18V XRP™
Includes	360° side handle, 7-1/4" carbide tipped circular saw blade, circular saw rip fence, reciprocating saw blade and kit box	360° side handle, 7-1/4" carbide tipped circular saw blade, circular saw rip fence and contractor bag	360° side handle, reciprocating saw blade and contractor bag	360° side handle, carbide tipped circular saw blade, circular saw rip fence and kit box	360° side handle, depth rod and kit box

CORDLESS COMBO KITS



18V Cordless 9-Tool Combo Kit 18V Cordless 9-Tool Combo Kit 18V Cordless 6-Tool Combo Kit 18V Cordless 6-Tool Combo Kit 18V Cordless 5-Tool Combo Kit

SPECIFICATIONS	D C9PAKRA	D C9PAKIA	D C6PAKRA	D C6PAKIA	D C5PAKA/D C5PAKVD
Voltage	18V	18V	18V	18V	18V
Hammerdrill/Drill/Driver	DC925	DC925	DC925	DC925	DC925
Circular Saw	DC390 (6-1/2")	DC390 (6-1/2")	DC390 (6-1/2")	DC390 (6-1/2")	DC390 (6-1/2")
Reciprocating Saw	DC385	DC385	DC385	DC385	DC385
Right Angle Drill	DW960	-	DW960	-	-
Out-Off Tool	DC410	DC410	DC410	DC410	-
Out-Out Tool	DC550	DC550	-	-	-
Jig Saw	DC330	DC330	-	-	DC330
Impact Driver	-	DW056	-	DW056	-
Impact Wrench	DW059	DW059	-	-	-
Flexible Floodlight	DW919	DW919	DW919	DW919	DW919
Charger/Batteries	1 hour / (2) 18V XRP™	1 hour / (2) 18V XRP™	1 hour / (2) 18V XRP™	1 hour / (2) 18V XRP™	1 hour / (2) 18V XRP™ *Adds vehicle charger & 3rd XRP™ battery
Includes	360° side handle, carbide tipped circular saw blade, circular saw rip fence, reciprocating saw blade, jig saw blades, type 1 and type 27 guards, wrench, backing flange, (1) type 1 wheel, 3-position side handle and (2) contractor bags	360° side handle, carbide tipped circular saw blade, circular saw rip fence, type 1 and type 27 guards, wrench, backing flange, (1) type 1 wheel, 3-position side handle, reciprocating saw blade and contractor bag	360° side handle, carbide tipped circular saw blade, circular saw rip fence, type 1 and type 27 guards, wrench, backing flange, (1) type 1 wheel, 3-position side handle, reciprocating saw blade and contractor bag	360° side handle, carbide tipped circular saw blade, circular saw rip fence, jig saw blades, reciprocating saw blade and kit box	360° side handle, carbide tipped circular saw blade, circular saw rip fence, jig saw blades, reciprocating saw blade and kit box

CORDLESS COMBO KITS



18V Cordless 2-Tool Combo Kit 18V Cordless 2-Tool Combo Kit 18V Cordless 4-Tool Combo Kit 18V Cordless Compact 2-Tool Combo Kit 18V Cordless Compact 2-Tool Combo Kit

SPECIFICATIONS	D C2PAKSA	D C2PAKCA	D C4CPKA	D C759CA	D C759SA
Voltage	18V	18V	18V	18V	18V
Hammerdrill/Drill/Driver	DC925	DC925	-	-	-
Drill/Driver	-	-	DC759	DC759	DC759
Circular Saw	DC390 (6-1/2")	-	DW936 (5-3/8")	-	DW936 (5-3/8")
Reciprocating Saw	-	DC385	DW938	DW938	-
Pivoting Head Flashlight	-	-	DW908	-	-
Charger/Batteries	1 hour / (2) 18V XRP™	1 hour / (2) 18V XRP™	1 hour / (2) 18V	1 hour / (2) 18V	1 hour / (2) 18V
Includes	360° side handle, carbide tipped circular saw blade, circular saw rip fence and kit box	360° side handle, reciprocating saw blade and kit box	carbide tipped circular saw blade, reciprocating saw blade and kit box	reciprocating saw blade and kit box	carbide tipped circular saw blade and kit box

6 <PREVIOUS

www.DeWALT.com

1-800-4 DeWALT

NEXT >