



HEAVY-DUTY POWER TOOLS

GUARANTEED TOUGH.

WORKSITE RADIO/CHARGER



Worksite Radio/Charger

SPECIFICATIONS	DC011
Power Source	7.2V to 18V Battery or AC Power
Radio Output	92 dB
AM/FM Digital Tuner	Yes
Auxiliary Port	Yes
Charge Time	1 hour or less
Tool Weight	13.2 lbs

WORKLIGHT/CHARGER



Cordless/Corded Worklight/Dual Port Charger w/GFCI Protection

SPECIFICATIONS	DC022
Power Source	12-18V Batteries or AC Power
Bulb	38W Fluorescent
Brightness	2700 Lumens
Charge Time	1 Hour or less
Run-Time	1-hour on 18V DC9096 Battery
Weight	12.0 lbs
Batteries	Sold Separately

FLUORESCENT AREA LIGHTS



18V Cordless Fluorescent Area Light 14.4V/12V Cordless Fluorescent Area Light

SPECIFICATIONS	DC527	DC528
Voltage	18V	14.4V OR 12V
Bulb	13 Watt	13 Watt
Run-Time	3.5 hrs	2.75 hrs
Weight	1.25 lbs	1.15 lbs
Battery	Sold Separately	Sold Separately

XENON FLOODLIGHTS



36V Cordless Floodlight 18V Cordless Flexible Floodlight 14.4V Cordless Flexible Floodlight

SPECIFICATIONS	DC509	DW919	DW918
Voltage	36V	18V	14.4V
Bulb	Xenon	Xenon	Xenon
Run-Time	8 hrs	3 hrs	3 hrs
Weight	1.14 lbs	.75 lbs	0.5 lbs
Battery	Sold Separately	Sold Separately	Sold Separately

FLASHLIGHTS



18V Cordless Pivoting Head Flashlight 14.4V Cordless Pivoting Head Flashlight 12V Cordless Pivoting Head Flashlight

SPECIFICATIONS	DW908	DW906	DW904
Voltage	18V	14.4V	12V
Bulb	Xenon	Xenon	Xenon
Run-Time	3 hrs	3 hrs	3 hrs
Tool Weight	0.5 lbs	0.5 lbs	0.5 lbs
Batteries	Sold Separately	Sold Separately	Sold Separately

BATTERIES/CHARGERS



1 Hour Charger w/ Auto. Tune-Up™ Mode Dual Port 1 Hour Charger 15 Minute Charger Worksite Radio/Charger 1 Hour Fan Cooled Charger 1 Hour Charger 1 Hour Vehicle Charger 1 Hour Fan Cooled Vehicle Charger

CAT #	VOLTAGE	DW9116	DW9216	DW9117	DC011	DW0246	DC9000	DW9109	DW0249
DC9360	36V	X	X	X	X	X	60	X	X
DW0242	24V	X	X	X	X	60	X	X	60
DC9096	18V	60	60	20	60	X	X	60	X
DC9091	14.4V	60	60	20	60	X	X	60	X
DC9071	12V	60	60	20	60	X	X	60	X
DW9061	9.6V	45	45	15	45	X	X	45	X
DW9057	7.2V	30	30	12	30	X	X	30	X

www.DEWALT.com

1-800-4 DEWALT