



CORDLESS POWER TOOLS

GUARANTEED TOUGH.

CUT-OFF TOOLS



4-1/2" (114mm) 36V Cordless Li-Ion Cut-Off Tool Kit



18V Cordless Cut-Off Tool Kit



18V Cordless Cut-Off Tool (Tool Only)

SPECIFICATIONS	DC415K	DC411KA	DC411B
Volts	36V	18V	18V
No Load Speed	6,500 rpm	6,500 rpm	6,500 rpm
Spindle Lock	Yes	Yes	Yes
Spindle Thread	5/8" - 11	5/8" - 11	5/8" - 11
Weight	72 lbs	70 lbs	4.6 lbs (tool only)
Charger/Batteries	1 Hour Charger / (2) 36V Li-Ion	1 Hour Charger / (2) 18V XRP™	Sold Separately
Includes	Type 27 guard, Type 1 guard, wrench, (2) matched flanges, Type 1 (cutting wheel) side handle	Type 1 guard, Wrench, (2) matched flanges, 2-position side handle	Type 1 guard, wrench, (2) matched flanges, 2-position side handle

BAND SAWS



18V Heavy Duty Cordless Li-Ion Band Saw



18V Heavy Duty Cordless Band Saw



18V Heavy Duty Cordless Band Saw (Tool Only)

SPECIFICATIONS	DCS370L	DCS370K	DCS370B
Volts	18V	18V	18V
R/Min	570 fpm	570 fpm	570 fpm
Blade Length	32-7/8"	32-7/8"	32-7/8"
Max Capacity	2-1/2"	2-1/2"	2-1/2"
Tool Length	15"	15"	15"
Weight	925 lbs	10 lbs	775 lbs
Charger/Batteries	1 Hour Charger / (1) 18V XRP™ Li-Ion	1 Hour Charger / (1) 18V XRP™	Sold Separately
Includes	14/18 blade blade tracking wrench	14/18 blade blade tracking wrench	14/18 blade blade tracking wrench

BI-METAL CORDLESS BANDSAW BLADES

CAT #	TPI	THICKNESS	LENGTH	HEIGHT	PACK
DW3982C	14	.020"	32-7/8"	1/2"	3
DW3983C	18	.020"	32-7/8"	1/2"	3
DW3984C	24	.020"	32-7/8"	1/2"	3
DW3986C	14/18	.020"	32-7/8"	1/2"	3

ADHESIVE DISPENSERS



18V Cordless Adhesive Dispenser - 300ml (Tool Only)



18V Cordless Adhesive Dispenser - 29oz (Tool Only)



18V Cordless Adhesive Dispenser - 10oz



18V Cordless Adhesive Dispenser - 10oz (Tool Only)

SPECIFICATIONS	DC547B	DC546B	DC545K	DC545B
Volts	18V	18V	18V	18V
Lbs of Force	650	650	650	650
Auto Reverse	Yes	Yes	Yes	Yes
'Set & Forget' Speed Control	Yes	Yes	Yes	Yes
Capacity	300ml & 600ml sausage packs	29oz, & quart size cartridges	10oz, 1/10gal, & 300ml-310ml cartridges	10oz, 1/10gal, & 300ml-310ml cartridges
Max. Speed	25 in/min	25 in/min	25 in/min	25 in/min
Weight	4.76 lbs (tool only)	5.51 lbs (tool only)	6.85 lbs	4.81 lbs (tool only)
Charger/Batteries	Sold Separately	Sold Separately	1 Hour Charger / (1) 18V	Sold Separately