

Hex Head Cap Screws Stainless Steel - PC 4010




- Hex Head Cap Screws
- Partial Thread
- 18-8 Stainless Steel

Stainless steel hex head cap screws are used in non-critical applications with nuts and washers. Length is determined from the base of the fastener head. 18-8 Stainless Steel is used where corrosion resistance is required. 18% chromium, 8% nickel.

| CAT NO | UPC | SIZE | HEX SIZE | STD | MSTR | WT/STD | UNIT |
|-----------|-------|--------------|----------|-----|------|--------|------|
| MBS1412 | 69704 | 1/4 x 1/2 | 7/16" | 100 | 4000 | 1.18# | C |
| MBS1434 | 69706 | 1/4 x 3/4 | 7/16" | 100 | 3000 | 1.44# | C |
| MBS141 | 69708 | 1/4 x 1 | 7/16" | 100 | 3000 | 1.67# | C |
| MBS14114 | 69710 | 1/4 x 1-1/4 | 7/16" | 100 | 1000 | 2.01# | C |
| MBS14112 | 69712 | 1/4 x 1-1/2 | 7/16" | 100 | 1000 | 2.36# | C |
| MBS142 | 69714 | 1/4 x 2 | 7/16" | 100 | 1000 | 3.07# | C |
| MBS51612 | 69744 | 5/16 x 1/2 | 1/2" | 100 | 1000 | 1.95# | C |
| MBS51634 | 69746 | 5/16 x 3/4 | 1/2" | 100 | 1000 | 2.33# | C |
| MBS5161 | 69748 | 5/16 x 1 | 1/2" | 100 | 1000 | 2.74# | C |
| MBS516114 | 69750 | 5/16 x 1-1/4 | 1/2" | 100 | 1000 | 3.23# | C |
| MBS516112 | 69752 | 5/16 x 1-1/2 | 1/2" | 100 | 1000 | 3.82# | C |
| MBS5162 | 69754 | 5/16 x 2 | 1/2" | 100 | 1000 | 4.82# | C |
| MBS3812 | 69804 | 3/8 x 1/2 | 9/16" | 100 | 1000 | 2.93# | C |
| MBS3834 | 69806 | 3/8 x 3/4 | 9/16" | 100 | 1000 | 3.55# | C |
| MBS381 | 69808 | 3/8 x 1 | 9/16" | 100 | 1000 | 4.03# | C |
| MBS38114 | 69810 | 3/8 x 1-1/4 | 9/16" | 100 | 1000 | 4.48# | C |
| MBS38112 | 69812 | 3/8 x 1-1/2 | 9/16" | 100 | 1000 | 5.54# | C |
| MBS382 | 69814 | 3/8 x 2 | 9/16" | 100 | 1000 | 6.94# | C |
| MBS1234 | 69844 | 1/2 x 3/4 | 3/4" | 50 | 500 | 3.63# | C |
| MBS121 | 69846 | 1/2 x 1 | 3/4" | 50 | 500 | 4.15# | C |
| MBS12114 | 69848 | 1/2 x 1-1/4 | 3/4" | 50 | 500 | 4.69# | C |
| MBS12112 | 69850 | 1/2 x 1-1/2 | 3/4" | 50 | 500 | 5.21# | C |
| MBS122 | 69852 | 1/2 x 2 | 3/4" | 50 | 500 | 6.73# | C |

Hex Head Tap Bolts Silicon Bronze - PC 4015



- Hex Head Tap Bolts
- Full Thread
- Silicon Bronze

Silicon bronze hex head tap bolts are used in non-critical applications with nuts and washers. Length is determined from the base of the fastener head. Silicon bronze is superior for marine applications. It will not corrode, is harder than brass and has a high resistance to extreme temperatures.

| CAT NO | UPC | SIZE | HEX SIZE | STD | MSTR | WT/STD | UNIT |
|------------|-------|--------------|----------|-----|------|--------|------|
| MBBZ1412 | 58300 | 1/4 x 1/2 | 7/16" | 100 | 4000 | 1.18# | C |
| MBBZ1434 | 58301 | 1/4 x 3/4 | 7/16" | 100 | 3000 | 1.44# | C |
| MBBZ141 | 58302 | 1/4 x 1 | 7/16" | 100 | 3000 | 1.67# | C |
| MBBZ14114 | 58303 | 1/4 x 1-1/4 | 7/16" | 100 | 1000 | 2.01# | C |
| MBBZ14112 | 58304 | 1/4 x 1-1/2 | 7/16" | 100 | 1000 | 2.36# | C |
| MBBZ142 | 58305 | 1/4 x 2 | 7/16" | 100 | 1000 | 3.07# | C |
| MBBZ51612 | 58308 | 5/16 x 1/2 | 1/2" | 100 | 1000 | 1.95# | C |
| MBBZ51634 | 58309 | 5/16 x 3/4 | 1/2" | 100 | 1000 | 2.33# | C |
| MBBZ5161 | 58310 | 5/16 x 1 | 1/2" | 100 | 1000 | 2.74# | C |
| MBBZ516114 | 58311 | 5/16 x 1-1/4 | 1/2" | 100 | 1000 | 3.23# | C |
| MBBZ516112 | 58312 | 5/16 x 1-1/2 | 1/2" | 100 | 1000 | 3.82# | C |
| MBBZ5162 | 58313 | 5/16 x 2 | 1/2" | 100 | 1000 | 4.82# | C |
| MBBZ3812 | 58316 | 3/8 x 1/2 | 9/16" | 100 | 1000 | 2.93# | C |
| MBBZ3834 | 58317 | 3/8 x 3/4 | 9/16" | 100 | 1000 | 3.55# | C |
| MBBZ381 | 58318 | 3/8 x 1 | 9/16" | 100 | 1000 | 4.03# | C |
| MBBZ38114 | 58319 | 3/8 x 1-1/4 | 9/16" | 100 | 1000 | 4.48# | C |
| MBBZ38112 | 58320 | 3/8 x 1-1/2 | 9/16" | 100 | 1000 | 5.54# | C |
| MBBZ382 | 58321 | 3/8 x 2 | 9/16" | 100 | 1000 | 6.94# | C |
| MBBZ1234 | 58326 | 1/2 x 3/4 | 3/4" | 50 | 500 | 3.63# | C |
| MBBZ121 | 58327 | 1/2 x 1 | 3/4" | 50 | 500 | 4.15# | C |
| MBBZ12114 | 58328 | 1/2 x 1-1/4 | 3/4" | 50 | 500 | 4.69# | C |
| MBBZ12112 | 58329 | 1/2 x 1-1/2 | 3/4" | 50 | 500 | 5.21# | C |
| MBBZ122 | 58330 | 1/2 x 2 | 3/4" | 50 | 500 | 6.73# | C |