


Hex Washer Head Self Drilling Screws Zinc Plated - PC 4220



- Self Drilling
- Hex Washer Head
- Zinc Plated Steel
- Invincibox™ Up To 2"

Hex washer head self drilling screws drill a hole and tap threads in one operation. The drilling operation removes metal and can be used in heavier gauge metals. Length is determined from the base of the fastener head.



CAT NO	UPC	SIZE	HEX SIZE	STD SLEEVE	MSTR	WT/STD	UNIT		
TEKHW612	17455	#6	6 x 1/2	1/4"	100	500	4000	0.26#	C
TEKHW634	17460		6 x 3/4	1/4"	100	500	4000	0.31#	C
TEKHW61	17465		6 x 1	1/4"	100	500	4000	0.37#	C
TEKHW812	17500		8 x 1/2	1/4"	100	500	4000	0.36#	C
TEKHW834	17505		8 x 3/4	1/4"	100	500	4000	0.46#	C
TEKHW81	17510	#8	8 x 1	1/4"	100	500	4000	0.56#	C
TEKHW8114	17515		8 x 1-1/4	1/4"	100	500	4000	0.68#	C
TEKHW8112	17520		8 x 1-1/2	1/4"	100	500	3000	0.74#	C
TEKHW82	17523		8 x 2	1/4"	100	500	3000	0.91#	C
TEKHW1012	17525		10 x 1/2	5/16"	100	500	4000	0.51#	C
TEKHW1034	17530		10 x 3/4	5/16"	100	500	4000	0.62#	C
TEKHW101	17535	#10	10 x 1	5/16"	100	500	4000	0.79#	C
TEKHW10114	17540		10 x 1-1/4	5/16"	100	500	3000	0.92#	C
TEKHW10112	17545		10 x 1-1/2	5/16"	100	500	3000	1.06#	C
TEKHW102	17547		10 x 2	5/16"	50	250	1500	0.66#	C
TEKHW1234	17550		12 x 3/4	5/16"	100	500	4000	0.89#	C
TEKHW121	17555		12 x 1	5/16"	100	500	3000	1.08#	C
TEKHW12112	17560	#12	12 x 1-1/2	5/16"	100	500	3000	1.44#	C
TEKHW122	17562		12 x 2	5/16"	50	250	1500	0.89#	C
TEKHW1434	17565		14 x 3/4	3/8"	100	500	3000	1.35#	C
TEKHW141	17570		14 x 1	3/8"	100	500	3000	1.39#	C
TEKHW14114	17575	#14	14 x 1-1/4	3/8"	100	500	3000	1.86#	C
TEKHW14112	17580		14 x 1-1/2	3/8"	50	250	1500	1.04#	C
TEKHW142	17585		14 x 2	3/8"	50	250	1500	1.16#	C
TEKHT812	17800	#8 Tuff Pack	8 x 1/2	1/4"	500		3000	2.04#	C
TEKHT834	17802		8 x 3/4	1/4"	500		3000	2.22#	C
TEKHT81	17804		8 x 1	1/4"	500		3000	2.76#	C
TEKHT1012	17806		10 x 1/2	5/16"	500		3000	2.48#	C
TEKHT1034	17808	#10 Tuff Pack	10 x 3/4	5/16"	500		3000	3.10#	C
TEKHT101	17810		10 x 1	5/16"	500		3000	3.74#	C

Phillips Wafer Head Self Drilling Screws Zinc Plated - PC 4220



- Self Drilling
- Wafer Head
- Phillips
- Zinc Plated Steel
- Invincibox™ Up To 1-1/4"

Self drilling phillips wafer head screws drill a hole and tap threads in one operation. The drilling operation removes metal and can be used with heavier gauge metals. Length is determined from the base of the fastener head.

CAT NO	UPC	SIZE	BIT SIZE	STD SLEEVE	MSTR	WT/STD	UNIT		
TEKW812	17775	#8	8 x 1/2	#2	100	500	4000	0.34#	C
TEKW834	17780		8 x 3/4	#2	100	500	4000	0.45#	C
TEKW81	81481		8 x 1	#2	100	500	4000	0.56#	C
TEKW8114	17785		8 x 1-1/4	#2	100	500	4000	0.67#	C
TEKWT812	17790	#8 Tuff Pack	8 x 1/2	#2	500		3000	2.04#	C
TEKWT834	17795		8 x 3/4	#2	500		3000	2.68#	C
TEKWT81	81482		8 x 1	#2	500		3000	2.80#	C
TEKW812BK	81483	#8 Bulk Pack	8 X 1/2	#2	10000		10000	34.00#	C
TEKW834BK	81484		8 X 3/4	#2	10000		10000	45.00#	C
TEKW81BK	81485		8 X 1	#2	6500		6500	29.25#	C
TEKW8114BK	81486		8 X 1-1/4	#2	6500		6500	30.55#	C